



Sample photo

Order symbol: TA292411
Product nbr: 5814003
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074060754
El. number:
Finland: 3435688
Denmark: 8212035069
Sweden: 5814003
Norway:

Including: Base with PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and plastic hinges.

Dimensions:				Rating:
Length	Width	Height		
mm: 289	239	107		Ingress Protection (EN 60529): IP 65
inch: 11.4	9.4	4.2		Impact Resistance (EN 62262): IK 07
Materials:				Electrical insulation: Totally insulated
Material:	ABS			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:	RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour:	RAL 7035			Glow Wire Test (IEC 695-2-1) °C: 650
Cover screws material:	Polyamide			Certificates:
Cover screws colour:	Grey			Fimko
Gasket material:	PUR			Gost R
Temperatures:				
Short term:	-40 ... 80 °C			
Continuous:	-40 ... 60 °C			
Short term:	-40 ... 175 °F			
Continuous:	-40 ... 140 °F			
Accessories:				
MP 2924	Mounting plate			
DR 215	DIN-35 Mounting rail			
DR 265	DIN-35 Mounting rail			
FP 10674	Wall fastening lug (2 pcs) incl. screws			
DPS 14553	Grey sealing plug set			

TEMPO 289x239x107

