



Quartz Crystal

32,768 kHz

SMD-version

model	KX-327NHT
frequency	32,768 kHz
operating temperature	-40° ~ +85°C
frequency tolerance at +25°C	± 20 ppm
temperature tolerance at -40° ~ +85°C	-0,035 ppm/°C ² typ.
storage temperature range	-55°C ~ +125°C
turnover temperature	+25°C ±5°C
load capacitance C _L	12,5 pF
motional capacitance (C1)	0,0036 pF, typ.
series resonance R ₁ max.	80k Ohm
aging (first year)	± 3 ppm max.
shunt capacitance C _O	1,6 pF typ.
drive level in µW max.	1,0 µW max. (0,1 typ)
quality factor (Q)	20000 min.
reflow soldering condition	10 seconds at +260°C max. (2 times max.)
RoHS	since production start
contents of reel	3000 pcs.
part no.	12.87150 ~ 12.87159

