

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301080162](#)  
**Status:** **Active**  
**Overview:** [Wide-Area Lighting Products](#)  
**Description:** Super-Safeway Twin Tube 64W Fluorescent Work Light with 16/3 SJOW 7.62m (25.0') Cord Length

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E174254

**General**

Product Family Portable Lighting  
 Series [130108](#)  
 NEMA Configuration NEMA 5-15  
 Outlet None  
 Overview [Wide-Area Lighting Products](#)  
 Product Name Super-Safeway  
 Type Wide Area Lamps  
 UPC 78678867148

**Physical**

Cord Length - Primary 7.62m (25.0')  
 Cord Length - Secondary N/A  
 Depth 190.75mm (7.510")  
 Duty Industrial  
 Guard Included No  
 Guard Type N/A  
 Height 82.55mm (3.250")  
 Length 1.39m (54.620")  
 Material - Globe Butyrate  
 Material - Guard Nitrile Rubber 80 Shore A  
 Mounting Style Adjustable Brackets  
 Packaging Type Carton  
 Socket Construction N/A

**Electrical**

Bulb Type Fluorescent  
 Cord Type - Primary 16/3 SJOW  
 Lamp Type F32/T8  
 Lamp Wattage - Maximum 64W  
 Lumens 5700  
 On/Off Switch No  
 Voltage (Fixture) - Maximum 120VAC 60 HZ

**Material Info**

Engineering Number 1350



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130108 Series](#)