



DW088K

2 Way Self-Levelling Line Laser (Horizontal and Vertical)

Selling Proposition

- Self-levelling cross line laser is accurate to ± 0.3 mm/m in levelling applications
- Self-Levelling up to 4 degrees surface angle with automatic out of level indication, marks a levelled line in seconds
- 2 button operation and low battery indication for ease of use
- Built in magnetic pivot bracket mounts easily on metal surfaces
- Overmolded housing and thick glass protects the tool and helps maintain calibration under jobsite conditions
- Includes 3 x AA batteries for 40 plus hours runtime

Standard Equipment

- 3 x AA size alkaline batteries
- Wall mount bracket
- Heavy duty carrying case

Warranty Specifications

- 30 Day Money Back Guarantee
- 1 Year Free Service Contract
- 1 Year Warranty

Specifications	
Type de laser	2, <1mW
Pøesnost	+/-0.3 mm/m
Number of beams	2
Direction of beams	vertical/level
Indoor Visibility Range	10 m
Self-Levelling Range	+/-4 °
Power Supply	4.5V - 3x AA
Tripod connection	1.4"