

Wiha 1/4" Socket Accessories



601 45 1/4" Reversible Ratchet Varicat - 32 Tooth

DIN 3122 D - ISO 3315

Forged body, satin finish, nickel and hard chrome.

Item			
No.	Inch	mm	wt.
601 45	5.5	140	.18



601 46 1/4" Reversing Ratchet - 20 Tooth, Push Through Type

20 tooth ratchet. DIN 3122 C - ISO 3315

Forged ratchet body, satin finish, nickel and hard chrome.

Item			
No.	Inch	mm	wt.
601 46	6.0	150	.18



601 31 1/4" Sliding T-handle

DIN 3122 A - ISO 3316

Hard chrome finish, fully polished with spring-loaded retaining ball.

Item			
No.	Inch	mm	wt.
601 31	4.5	114	.09



601 1/4" Extension Bar

DIN 3123 B - ISO 3316

Hard chrome finish, fully polished with spring-loaded retaining ball.

Item			
No.	Inch	mm	wt.
601 32	2.17	50	.05
601 33	3.93	100	.10
601 34	5.90	150	.14



601 35 1/4" Wobble Extension

Hard chrome finish, fully polished with spring-loaded retaining ball.

Item			
No.	Inch	mm	wt.
601 35	3.93	100	.10



601 36 1/4" Universal Joint

Hard chrome finish, fully polished with spring-loaded retaining ball.

Item			
No.	Inch	mm	wt.
601 36	1.4	35	.05



601 37 1/4" Swivel Handle

Hard chrome finish, fully polished with spring-loaded retaining ball.

Item			
No.	Inch	mm	wt.
601 37	6.10	155	.25



601 38 1/4" Spinner Handle

Hard chrome finish, fully polished with spring-loaded retaining ball.

Item			
No.	Inch	mm	wt.
601 38	6.10	155	.25



601 39 1/4" Flexible Extension

Hard chrome finish.

Item			
No.	Inch	mm	wt.
601 39	4.72	120	.11



601 40 1/4" Converter To 3/8"

Hard chrome finish, fully polished with spring-loaded retaining ball.

Item			
No.	Inch	mm	wt.
601 40	1.06	27	.04



601 41 1/4" Square Coupler

Hard chrome finish, fully polished with spring-loaded retaining ball.

Item			
No.	Inch	mm	wt.
601 41	.79	20	.01