


ALL DIMENSIONS ARE
FOR REFERENCE ONLY

DIMENSIONS ARE IN INCHES [MILLIMETERS]
UNLESS OTHERWISE NOTED



SPECIFICATIONS

SHIPPING WEIGHT 2.4 POUNDS [1.09 KG]

MATERIAL:

1. GEAR RACK MILD STEEL,
3/4 [19] SQUARE
BLACK OXIDE FINISH ON TEETH
GROUND FINISH THREE SIDES
2. BASE ASSEMBLY (PN S506-100) .
BASE PLATE 6061-T6 ALUMINUM
BOTTOM PLATE 6061-T6 ALUMINUM
SCREWS (4 EA) ... 10-32 X 7/8 FLAT HEAD
STEEL SCREW
ZINC PLATED
SPACERS (4 EA) .. #10 X 9/16
6061-T6 ALUMINUM
NATURAL FINISH
3. CABLE GUIDE ASSY (PN S506-120)
CABLE GUIDE EXTRUDED 6063-T5 ALUMINUM
THUMB SCREW 6-32 X 3/4
STEEL THUMB SCREW
ZINC PLATED
4. PLATEN ASSY (PN S506-110)
PLATEN 6061-T6 ALUMINUM
STUD 1/4 X 3/4 12L14 STEEL
NATURAL FINISH
ROLL PIN STEEL
BLACK OXIDE

NOT SHOWN:

- SCREWS (2 EA) 1/4-20 X 3/4
FLAT HEAD STEEL
ZINC PLATED

ALL DESIGN, OPERATIVE, AND PROCESS DATA PERTAINING TO THE ARTICLE ON THIS SHEET IS THE PROPERTY OF PANAVISE PRODUCTS, INC., RENO, NV. THIS INFORMATION IS DISCLOSED IN CONFIDENCE AND IS NOT TO BE COPIED, REPRODUCED, OR REVEALED TO OR APPROPRIATED BY OTHERS, IN PART OR IN WHOLE, WITHOUT THE EXPRESSED CONSENT OF PANAVISE. THIS PRINT IS LOANED, AND MUST NOT BE USED IN ANY MANNER DETRIMENTAL TO THE INTEREST OF PANAVISE, AND MUST BE RETURNED ON DEMAND



PANAVISE®

7540 Calbert Drive, Reno, Nevada 89511-1225
Phone (702) 850-2900, Fax (702) 850-2929

TITLE

RETROFIT KIT FOR
PANAVISE ARBOR PRESS

BASIC DIM. ENGLISH [ALTERNATE DIM. METRIC]

DRAWN	DATE	SCALE	SHT	OF
I BENNETT	AUG 96	NONE	1	1

SIZE
A

DWG. NO.

506 SP

REV

A