

8.5 ± .062  
[216 ± 1.6]

2

LASER INK-JET LABELS  
5050X125YAJ

PRINTER LEAD EDGE  
FEED IN THE DIRECTION

2

0.50 ± .062  
[12.70 ± 1.6]  
TYP. 13 PLCS.

2

CLEAR AREA

0.50 ± .062  
[12.70 ± 1.6]  
TYP. 6 PLCS.

1.50 ± .062 [38.10 ± 1.6]  
TYP. 6 PLCS.

2

11.0 ± .062 [279 ± 1.6]

2

WHITE IMPRINT AREA

| PART NUMBER | MATERIAL                           | MARKER SIZE<br>inches [ mm ]          | LABELS PER<br>SHEET | SHEET<br>QTY. | STANDARD<br>PKG. QTY. |
|-------------|------------------------------------|---------------------------------------|---------------------|---------------|-----------------------|
| S050X150YAJ | 6MY6<br>CLEAR<br>POLYESTER<br>FILM | 0.500 [ 12.7 ]<br>X<br>1.500 [ 38.1 ] | 78                  | 65            | 5000                  |

|                                                                                                                                                                                                          |                              |                                                                                               |                           |                  |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------|-----------------------------------------------------------------------------------------------|---------------------------|------------------|
| CAD FILENAME/LAYERS                                                                                                                                                                                      |                              | I00472CB_DC_C I0202/02C                                                                       |                           |                  |
| PANDUIT CORP. TINLEY PARK, ILLINOIS                                                                                                                                                                      |                              |                                                                                               |                           |                  |
| CUSTOMER DRAWING OPTIMUMM SELF-LAM.<br>LASER INKJET PRINTABLE LABELS                                                                                                                                     |                              |                                                                                               |                           |                  |
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE:<br><br>(.X) ± .12 (XXX) ± .025<br>(.XX) ± .062 ANGLES ±  |                              | UNLESS OTHERWISE SPECIFIED,<br>ALL DIMENSIONS ARE GIVEN<br>IN INCHES, THIRD ANGLE PROJECTION. |                           |                  |
| DRAWN BY<br>RVU                                                                                                                                                                                          | MAT'L ;<br><br><br>SEE TABLE |                                                                                               | SCALE<br>NTS              |                  |
| DATE<br>9/22/04                                                                                                                                                                                          |                              |                                                                                               | DRAWING NO.<br><br>C10202 | DWG<br>A<br>SIZE |
| CHK'D                                                                                                                                                                                                    |                              |                                                                                               |                           |                  |