





PRUEF 2

datasheet for PRUEF 2
article number: 973368101



[View Full-Size Image](#)

product description:		order number: 973 368-101
description:	Test tip with shatter-proof insulated sleeve. Insulation and oxide layers can be penetrated by the slender stainless steel tip. 4mm diameter brass socket connection. Accessory (optional): tip protector, IC-tap SS 260	
typ:	PRUEF 2 rot / red	
system:	4 mm system	
order number:	973 368-101	
color		
other color versions:		
technical data		
measurement category acc. to IEC 61010:	CAT I	
pin dimensions	2 mm	
type of contact:	test tip (unsprung)	
type of termination:	4 mm socket (unsprung)	
rated voltage:	30 VAC / 60 VDC	
rated current:	1 A	
Please consider derating curve!		
contact resistance:	50 mOhm	
material		
contact material:	tip: stainless steel socket: brass	
contact surface material:	tip: nickel	
housing material:	PP	
environmental conditions:		
temperature range:	-20 °C to +80 °C	
inflammable class:		
housing (basic material):	UL 94 HB	
drawing		

main menu



- home
- test & measurement
- products
- skills
- download

online catalogue T&M

- clamp-type test probes
- crocodile clips
- test probes
 - > 0,64 mm system
 - > 2 mm system
 - > 2 mm Sicherheitssystem
 - > 4 mm system
 - > 4 mm sliding sleeve system
 - > 4 mm safety system

- oscilloscope test probes
- measuring leads

plugs

sockets

sets

miscellaneous

company

portrait

corporate association

location maps

fairs and exhibitions

jobs

imprint

terms and conditions