

► Heatsinks f.cool

► Cases f.case

▼ Connectors f.con

► Sockets

▼ PCB connectors

- Male headers
- Female headers
- Direct female connector
- Jumpers

► IDC-connectors

► D-Sub connectors

■ Brackets for PC

► Optoelectronics


Male headers

SL 1 ... / SL 11 ...

SL 1 025 2 G

one row, □ 0.635 mm

add to request



Features

Technical Drawing

Variants

Accessories / related products

no. of contacts	2
contact material	CuSn alloy
surface contact / contact sleeve	Ni+≥0.2µm Au Ni+4...6µm Sn
surface of contact	gold-plated
volume resistivity	≤5 mΩ
nominal current	3 A
nominal voltage	250 VAC
test voltage	2000 V
material isolation body	PA4.6, GF
temperature range	-40°C... +163°C (260 °C / 10 s)
class of flammability	UL 94 V0
insulation resistance	>10 ¹² Ω
connection type	soldering
version	standard
reflow solderable	yes