


PRODUCT NO.
SEE TABLE



NOTES:

- 1 MADE IN ACCORDANCE WITH PRODUCT SPEC. BUS-12-001.
- 2 COLOR TO BE LIGHT BLUE WITH DARK BLUE TRACER ON EDGE OF FIRST POSITION ONLY
- 3 UL LISTED STYLE 2651. CSA CERTIFIED PER C22.2 (LATEST REVISION).

mat'l. code				surface ISO 1302		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE					
ltr	ecn no	dr	date	tolerances unless otherwise specified						title					
A	—	TB	11/28/84	angles	linear	.XX±.01/.3				INCH/MM	#28 AWG SOLID DOUBLE SCALLOPED PVC RD. COND. CABLE				
B	V82043	RGD	11/13/98			.XXX±.005/.13									
C	M06-0282	MHT	7/26/06			.XXX±.0020/.05									
				0'±2'				scale 1:1							
				dr	—	11/28/84			dwg no			sheet 1 of 2		size	
				enrg	R.DOUTRICH	11/28/84			77060			A3			
				chr	R.DOUTRICH	11/28/84									
				appd	R.DOUTRICH	11/28/84									
sheet index		revision sheet		C	C										
				1	2										

PRODUCT NO.
77060-XXX

77060-XXX

NO. OF CONDUCTORS
(MIN. 9, MAX 64)
LENGTH

TOLERANCE FOR DIMS		
NO. OF CONDUCTORS	DIM. A±	DIM. B±
9 THRU 15	.007/.18	.010/.25
16 THRU 37	.009/.23	.015/.38
38 THRU 64	.011/.28	.015/.38

X	MIN. LENGTH FT/M
0	100/30.48
1	100/30.48
3	300/91.44
4	300/91.44

mat'l. code				surface ISO 1302 ☒		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE									
ltr	ecn	no	dr	date	tolerances unless otherwise specified					title									
C					angles	linear	.XX±.01/.3		INCH/MM		#28 AWG SOLID DOUBLE SCALLOPED								
							.xxx±.005/.13				PVC RD. COND. CABLE								
					0'±2'		.xxx±.0020/.051		scale 1:1		dwg no								
					dr	-	11/28/84				sheet2 of 2 size								
					enr	R.DOUTRICH	11/28/84				77060								
					chr	R.DOUTRICH	11/28/84				A3								
					app	R.DOUTRICH	11/28/84				type Product Customer Drawing								
sheet index		revision sheet																	

form: A3