

VS-15-DSUB-20-LI-5,0

Order No.: 1656288

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1656288>

Assembled D-SUB cable shielded, 15-pos., stranded (7-wire), cable color RAL 7000 (gray), IP20 degree of protection, head 1 with socket shell 2 and straight cable outlet, head 2 with pin shell 2 and straight cable outlet, length: 5 m

Commercial data

GTIN (EAN)	 4 046356 029766
sales group	D505
Pack	1 pcs.
Customs tariff	85444290
Catalog page information	Page 326 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
09/19/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Mechanical characteristics

Number of positions	15
Insertion/withdrawal cycles	≥ 50
External cable diameter	6 mm
Cable exit	Straight
Length of cable	5 m
Ambient temperature (operation)	0 °C ... 70 °C

Material data

Housing material	PVC
Contact material	Copper alloy
Contact surface material	Gold-plated
Outer sheath, material	PVC
Degree of protection	IP20

Electrical characteristics

Rated voltage (III/3)	125 V
Rated current	1 A

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2011 Phoenix Contact
Technical modifications reserved;