


SWITCHES ROCKER

SPECIFICATIONS:

Current Rating:		20A @ 125V AC, 10A @ 277V AC 1-1/2 HP @ 125-250V AC			
Initial Contact Resistance:		5 Meg ohm (Max.)			
Insulation Resistance:		100 Meg ohm (Min.)			
Dielectric Strength:		1000V AC for 1 minute			
Gasket:		Molded Elastomer			
Case:		UL94 Flame Class, 94V-2			
Contact Material:		Brass			
Terminal Material:		Brass			
Terminal Type:		.250" Quick Connect			
Part No.	Type	Action			Actuator
30-630	DPST	ON	-	OFF	Black Nylon
30-660	DPST	(ON)	-	OFF	Black Nylon
30-640	DPDT	ON	-	ON	Black Nylon
30-680	DPDT	ON	-	(ON)	Black Nylon
30-650	DPDT	ON	OFF	ON	Black Nylon
30-690	DPDT	ON	OFF	(ON)	Black Nylon
30-695	DPDT	(ON)	OFF	(ON)	Black Nylon

NOTE: () = Momentary

DOUBLE POLE HEAVY DUTY ROCKER SWITCHES (Moisture and Dust Resistant)




Recommended Mounting Hole:
 $\pm .015$ $\pm .381$ $\pm .005$ $\pm .127$
 Fits .830 (21.08) x 1.450 (36.83) panel cutout in
 .093 (2.36), .125 (3.18), .187 (4.75) thick panels.



SPECIFICATIONS:

ELECTRICAL RATINGS:					
20A	125-250V AC 85C	UL E45221			
1/2HP	125V AC 1HP 250V AC	UL/CSA			
20A	125-250V AC	CSA LR10990			
16 (4)A	250V AC T85	VDE 62411			
16 (6)A	250V AC T125 5E4	Semko EN61058-1			
150A	Inrush	Semko IEC65			
20A	28V DC	Approvals N/A			
MATERIALS:					
Body:	Nylon 6.6				
Actuator:	Nylon 6.6				
Contact Gap:	3mm (.118)				
Contact Material:	Silver Alloy				
Part No.	Type	Action		Actuator	
30-564	DPST	ON	-	OFF	Black Nylon



Mounting Hole: 1.0" x 1.12"


ROCKER SWITCH



ROCKER SWITCH with LED

SPECIFICATIONS:

Current Rating:		10A @125V AC			
Initial Contact Resistance:		20 Meg ohm (Max.)			
Insulation Resistance:		500V DC 100 Meg ohm (Min.)			
Dielectric Strength:		1000V AC for 1 minute			
Contact Material:		Brass - Bright Nickel Plate			
Terminal Material:		Brass - Bright Nickel Plate			
Terminal Type:		.250" Quick Connect			
Part No.	Type	Action			Actuator
30-084	SPST	ON	-	OFF	White w/ Red LED



Mounting Hole: 0.430" x 1.180"




ROCKER SWITCHES with LED

SPECIFICATIONS:

Current Rating:		6A @125 V AC, 3A @ 250 V AC			
Initial Contact Resistance:		DC 2.5V-1A, 20 Meg ohm (Max.)			
Insulation Resistance:		500V DC 100 Meg ohm (Min.)			
Dielectric Strength:		1500V AC for 1 minute			
Contact Material:		Copper - Silver Plate			
Terminal Material:		Copper - Silver Plate			
Terminal Type:		Solder			
Part No.	Type	Action			Actuator
30-10083	SPST	ON	-	OFF	Black Nylon w/ Red LED
30-10085	SPST	ON	-	OFF	Black Nylon w/ Green LED
30-16081*	SPST	ON	-	OFF	Black Nylon w/Amber LED

*30-16081 has .187" Quick Connect Terminal



Mounting Hole: 0.51" x 0.75"

