





LEAD FINISH: SILVER	
BUSHING FINISH: SILVER	
CAPACITANCE	1200pF GMV
TEMP. RANGE	-55°C TO 125°C
CURRENT	10 AMP MAX.
WORKING VOLTAGE	85°C 300VDC MAX. 125°C 200VDC MAX.
D.C. RESISTANCE	.005ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	

FREQ. MHz	I.L. (db)
10	5
30	--
100	20
1 GHz	35
10 GHz	45



MARKING:

PART: S122P
 BAG:
 SCI 9900-381-6022
 DATE CODE
 LOT NO.
 QTY./BAG (100 MAX.)

- NOTES:
1. SUGGESTED MOUNTING HOLE = ϕ .120
 2. HARDWARE IS INCLUDED.

	09	08	07	06	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	 ERIE, FAIRVIEW PENNSYLVANIA	
	CN 201308	CN 200400	CN 188512	CN. 185004	CHANGE NOTICE	Fractions ± 1/64	SPECTRUM CONTROL INC.	
Dec. .xx±						Dwn. JKAUFFMAN	Description FEED THRU	
Dec. .xxx±.010						Ckd. 4/23/01	RESIN SEAL FILTER	
Angles ±0° 30'						Apvd.	9900-381-6022	
CODE IDENT. NO. DLSP2						Scale NONE		