

Shrink sleeve - WMS 4,8 (30X9)RXL - 0800395

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Shrink sleeve, Roll, white, Unlabeled, Can be labeled with: Thermomark W, Thermomark R, Thermomark X, Perforated, Mounting type: Slide on, Cable diameter: 1.6-4.8 mm, Lettering field: 30 x 9 mm

The illustration shows WMS 6,4 (30X10)R

Key commercial data

Packing unit	1
Minimum order quantity	8
Catalog page	Page 165 (CL2-2011)
GTIN	 4 046356 626620
Custom tariff number	39173200
Country of origin	CHINA

Technical data

General

Length (b)	30 mm
Width (a)	9 mm
Color	white
Base element material	polyolefine
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-55 °C ... 125 °C
Components	Halogen-free
Material	Polyolefine
Number of individual labels	5000
Number of individual labels per row	2

Classifications

eclass

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27149103

Shrink sleeve - WMS 4,8 (30X9)RXL - 0800395

Classifications

eclass

eCl@ss 6.0	27400401
eCl@ss 7.0	27400401

etim

ETIM 4.0	EC001530
----------	----------

unspsc

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Ink ribbon - THERMOMARK-RIBBON 64-WMSE - 5145724



Ink ribbon, Length: 300000 mm, Width: 64 mm, Color: black

Ink ribbon - THERMOMARK-RIBBON 64-WMSE BU - 5145737



Ink ribbon, Length: 300000 mm, Width: 64 mm, Color: blue

Ink ribbon - THERMOMARK-RIBBON 64-WMSE RD - 5145740



Ink ribbon, Length: 300000 mm, Width: 64 mm, Color: red