




LOC AR	DIST 35	REVISIONS													
		P	F	ZONE	LTR	DESCRIPTION				DATE	APPD				
					H	REV PER ECN BD4386				12-6-90	-				
					J	REV PER EC 0020-1041-93				12/01/93	JS				
					K	OBS 1--3 PER EC 0020-933-93				03/15/94	DK				
					L	OBSOLETE -14				21 AUG 97	JGH				
						PER EC 0410-197-96									

- 1 UL RATED 94V-0 THERMOPLASTIC, COLOR: BLACK.
- 2 PHOSPHOR BRONZE PER QQ-B-750.
- 3 PLATED WITH .000015 GOLD ON LOCALIZED GOLD PLATE AREA, .000100 - .000200 BRIGHT TIN LEAD ON TERMINATION END, ALL OVER .000050 NICKEL ON ENTIRE CONTACT.
- 4 POLARIZING FEATURE DOES NOT EXIST ON SAME END AS THE POSN #1 INDICATOR ON 10 AND 14 POSN PRODUCT.



TERMINATED VIEW



DETAIL Z
SCALE 10:1
TYPICAL

OBSOLETE	1.700	1.980	1.750	35	36	1-499997-4
OBSOLETE	2.100	2.380	2.150	43	44	1-499997-3
	3.100	3.380	3.150	63	64	1-499997-2
	2.900	3.180	2.950	59	60	1-499997-1
	2.400	2.680	2.450	49	50	1-499997-0
	1.900	2.180	1.950	39	40	1-499997-9
	1.600	1.880	1.650	33	34	1-499997-8
	1.400	1.680	1.450	29	30	1-499997-7
	1.200	1.480	1.250	25	26	1-499997-6
	1.100	1.380	1.150	23	24	1-499997-5
	.900	1.180	.950	19	20	1-499997-4
	.700	.980	.750	15	16	1-499997-3
	.600	.880	.650	13	14	1-499997-2
	.400	.680	.450	9	10	1-499997-1
	D	C	B	A	NO OF POSN	PART NUMBER

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON :		DR	J. PEACHEY	2-19-86	AMP INCORPORATED Harrisburg, Pa. 17105	
2 PL DEC ±.005		CHK	JAY SAUDER	3-18-86		
3 PL DEC ±.005		APPD	JAY SAUDER	3-18-86	NAME RECEPTACLE KIT, AMP-LATCH NOVO, MIL PLZN, 15 GOLD DUPLEX CONTACTS, W/O STRAIN RLF	
ANGLES ±5°		APPD	D. HOFFMAN	3-18-86		
MATERIAL		PRODUCT SPEC	108-40000	SIZE	F5CM NO	DRAWING NO
MOLDED PARTS:		APPLICATION SPEC	114-40005	D	00779	499997
CONTACTS:		WEIGHT	-	SCALE	4:1	SHEET 1 of 1