



[Home](#)
[About KSS](#)
[Contact Us](#)
[What's New](#)
[Our Products](#)
[Search](#)

0301 WEATHER RESISTANT NYLON CABLE TIE



Cabonate A was added for greater resistance to ultra violet in outdoor usage. Prolongs useful life of cable tie under sunshine/outdoor application.



Unit:mm

	Item No.		Length		Width	Max. Bundle Dia.	Min. Tensile Strength	
	100 pcs	1000 pcs	m.m.	inch	m.m.	m.m.	lbs(kgs)	
	☐ CV-075W	☐ CV-075KW	75	3"	2.4	18	18 (8)	MINIATURE
NEW	☐ CV-080W	☐ CV-080KW	80	3 1/8"	2.4	19	18 (8)	MINIATURE
	☐ CV-094W	☐ CV-094KW	96	3 3/4"	2.5	23	18 (8)	MINIATURE
	☐ CV-100W	☐ CV-100KW	100	4"	2.5	25	18 (8)	MINIATURE
	☐ CV-120SW	☐ CV-120SKW	120	4 3/4"	2.5	30	18 (8)	MINIATURE
	☐ CV-140SW	☐ CV-140SKW	142	5 1/2"	2.5	35	18 (8)	MINIATURE
NEW	☐ CV-150SW	☐ CV-150SKW	155	6 1/8"	2.5	39	18 (8)	MINIATURE
	☐ CV-165W	☐ CV-165KW	165	6 1/2"	2.5	44	18 (8)	MINIATURE

	☐ CV-200MW	☐ CV-200MKW	203	8"	2.5	55	18 (8)	MINIATURE
	☐ CV-400SW		400	15 3/4"	2.5	117	18 (8)	MINIATURE
	☐ CV-120W	☐ CV-120KW	120	4 3/4"	3.2	30	40 (18)	INTERMEDIATE
	☐ CV-140W	☐ CV-140KW	142	5 1/2"	3.2	35	40 (18)	INTERMEDIATE
	☐ CV-150W	☐ CV-150KW	150	6"	3.6	39	40 (18)	INTERMEDIATE
	☐ CV-180W	☐ CV-180KW	180	7"	3.6	49	40 (18)	INTERMEDIATE
	☐ CV-200SW	☐ CV-200SKW	203	8"	3.2	55	40 (18)	INTERMEDIATE
	☐ CV-200AW	☐ CV-200AKW	203	8"	3.6	55	40 (18)	INTERMEDIATE
	☐ CV-250MW	☐ CV-250MKW	250	10"	3.6	74	40 (18)	INTERMEDIATE
	☐ CV-265W	☐ CV-265KW	265	10 1/2"	3.6	78	40 (18)	INTERMEDIATE
	☐ CV-292W	☐ CV-292KW	292	11 1/2"	3.6	85	40 (18)	INTERMEDIATE
	☐ CV-330W		330	13"	3.6	96	40 (18)	INTERMEDIATE
	☐ CV-368SW		368	14 1/2"	3.6	102	40 (18)	INTERMEDIATE
	☐ CV-120LW	☐ CV-120LKW	120	4 3/4"	4.8	30	50 (22)	STANDARD
	☐ CV-160LW	☐ CV-160LKW	160	6 1/2"	4.8	42	50 (22)	STANDARD
	☐ CV-190W	☐ CV-190KW	190	7 1/2"	4.8	52	50 (22)	STANDARD
	☐ CV-200W	☐ CV-200KW	203	8"	4.6	55	55 (22)	STANDARD
	☐ CV-250W	☐ CV-250KW	250	10"	4.8	74	50 (22)	STANDARD
	☐ CV-280W	☐ CV-280KW	280	11"	4.8	81	50 (22)	STANDARD
	☐ CV-300SW		300	11 5/8"	4.8	85	50 (22)	STANDARD
	☐ CV-310W		310	12"	4.8	89	50 (22)	STANDARD
	☐ CV-368W		368	14 1/2"	4.8	102	50 (22)	STANDARD
	☐ CV-385W		385	15 3/16"	4.8	116	50 (22)	STANDARD
	☐ CV-432W		432	17"	4.8	125	50 (22)	STANDARD
	☐ CV-450MW		450	17 3/4"	4.8	130	50 (22)	STANDARD
	☐ CV-500W		500	17 11/16"	4.8	150	50 (22)	STANDARD
	☐ CV-							

.	914SW	.	914	36"	4.8	270	50 (22)	STANDARD
NEW	☐ CV-380S	.	380	15"	6.4	110	100 (45)	STANDARD
NEW	☐ CV-120LL	☐ CV-120LLK	120	4 3/4"	7.6	30	120 (55)	HEAVY DUTY
.	☐ CV-150LW	☐ CV-150LKW	150	6"	7.6	39	120 (55)	HEAVY DUTY
.	☐ CV-200LW	☐ CV-200LKW	203	8"	7.6	55	120 (55)	HEAVY DUTY
.	☐ CV-240LW	☐ CV-240LKW	240	9 7/16"	7.6	66	120 (55)	HEAVY DUTY
.	☐ CV-280LW	☐ CV-280LKW	280	11"	7.6	78	120 (55)	HEAVY DUTY
.	☐ CV-300W	.	300	11 7/8"	7.6	88	120 (55)	HEAVY DUTY
.	☐ CV-340W	.	340	13 1/2"	7.6	99	120 (55)	HEAVY DUTY
.	☐ CV-380W	.	380	15"	7.6	110	120 (55)	HEAVY DUTY
.	☐ CV-450W	.	450	17 3/4"	8.0	133	175 (80)	HEAVY DUTY
.	☐ CV-550W	.	550	21 11/16"	8.0	166	175 (80)	HEAVY DUTY
.	☐ CV-610W	.	605	24"	9.0	185	175 (80)	HEAVY DUTY
.	☐ CV-685W	.	680	27"	9.0	210	175 (80)	HEAVY DUTY
.	☐ CV-710W	.	705	28"	9.0	220	175 (80)	HEAVY DUTY
.	☐ CV-762W	.	762	30"	9.0	236	175 (80)	HEAVY DUTY
.	☐ CV-812W	.	812	32"	9.0	246	175 (80)	HEAVY DUTY
.	☐ CV-914W	.	914	36"	9.0	270	175 (80)	HEAVY DUTY
.	☐ CV-1168W	.	1168	46"	9.0	360	175 (80)	HEAVY DUTY
.	☐ CV-1219W	.	1219	48"	9.0	380	175 (80)	HEAVY DUTY
.	☐ CV-550LW	.	550	21 11/16"	12.7	166	250 (114)	HEAVY DUTY

[Check Selected](#) [Return All Selected](#)



Kai Suh Suh Enterprise Co., Ltd.