



A

The APart MASK loudspeakers have been designed for the contractor market and supply you with a crystal clear sound, from back ground music up to "dance level" music.

MASK8 has a unique and very stylish innovative design. The curved fine metal grill together with the shape of the wooden delta cabinet gives MASK8 a different, yet inconspicuous look.

MASK8 has a very powerfull 8" coated papercone woofer. Together with the ferro-fluid cooled silk dome tweeter on a Waveguide horn, this results in a high SPL, an ultra low distortion and a sound that comes close to studio monitor quality!

MASK8 loudspeakers can be used as full range loudspeakers, however we advise to use them in combination with the APart subwoofers SUB-2200 or SUB-2400. Its wide frequency range makes sure every note, starting from the punchy bass over the clean middle range to the crystal clear highs, reaches your ears with an astonishing clarity.

In combination with the Apart 3-channel amplifier PUBDRIVE2000 and the Apart SUB2400 passive subwoofer, MASK8 turns into a very performant system solution with impressive dB-levels.

The build-in Auto-Reset 3-step Protection Guard together with the quality components make MASK8 a fail-safe loudspeaker, even at high power loads!

MASK8 is delivered with a metal U-mounting bracket. After mounting the bracket on the wall, the sleeve in the bracket makes it quite easy and safe to fix the MASK8 loudspeakers, even in uncomfortable positions. The MASK8 cabinet has several thread mounting points tapped at the back, the top and side of the cabinet. This way the cabinet can be rigged or mounting clamps can be used. An extra contractor advantage!

MASK8 is available in black (Ref; MASK8-BL) and white (Ref; MASK8-W). They can be painted in any RAL colour as an option. (Ref; PAINT-CAB8, minimum order quantity is 12 pieces)

# APart MASK8 DESIGN SPEAKER



## TECHNICAL SPECIFICATIONS

Type	2-way HiFi Pro, bass reflex
Cabinet	MDF Wood
Woofer	8" HD Type
Tweeter	1" HD silk dome on Waveguide
Impedance	8 Ohm
RMS Power 8 Ohm	200 watt
AES Rated	300 watt
Music - Program	600 watt
Dynamic Peak (lo-cut)	
Protection system	Auto-Reset 3-step Protection Guard
SPL 1 watt/1 m	93 dB
SPL Max peak	124 dB
Frequency Range	60 Hz - 30 kHz
Dispersion	80° H x 70° V
IP rating	Indoor use only (IP 40)
Mounting points:	
Back	2
Top/bottom	1 / 1
Left/right side	2 / 2
Thread size mounting points	M8
Dimensions (H x W x D)	411 x 250 x 250 mm
Weight	8.1 Kg