





## SPECIFICATIONS

| PARAMETERS                  | VALUES        | UNIT  |
|-----------------------------|---------------|-------|
| RATED VOLTAGE               | 12            | Vdc   |
| OPERATING VOLTAGE RANGE     | 9 ~ 15        | Vdc   |
| TONE OUTPUT @ 12Vdc         | 93 ~ 95       | dBA   |
| CURRENT CONSUMPTION @ 12Vdc | 60            | mA    |
| INGRESS PROTECTION          | IP55          | -     |
| GONG MATERIAL/COLOR         | STEEL/RED     | -     |
| BASE MATERIAL               | POLYCARBONATE |       |
| OPERATING TEMPERATURE       | -10 ~ +55     | °C    |
| WEIGHT                      | 110           | grams |

THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.  
©2003, Projects Unlimited Inc.

## REVISION HISTORY

| LTR | DESCRIPTION                              | DATE       | APPROVED |
|-----|------------------------------------------|------------|----------|
| -   | RELEASED FROM ENGINEERING                | 12/28/2007 |          |
| A   | ADDED RoHS NOTE                          | 5/22/2007  | R.W.     |
| B   | REVISED TO INVENTOR 3-D DRAWING TEMPLATE | 6/28/2010  | B.R.     |



### NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.
3. THIS PART IS RoHS 2002/95/EC COMPLIANT.

|                                                                                                                  |      |                                                                                                                                            |            |            |             |             |            |            |
|------------------------------------------------------------------------------------------------------------------|------|--------------------------------------------------------------------------------------------------------------------------------------------|------------|------------|-------------|-------------|------------|------------|
| UNLESS OTHERWISE SPECIFIED:<br><br>DIMENSIONS ARE IN MILLIMETERS,<br><br>TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°. | SIZE | Designed by                                                                                                                                | Date       | Checked by | Date        | Approved by | Date       | Drawn Date |
|                                                                                                                  |      | J.A.F.                                                                                                                                     | 12/16/2005 | E.P.       | 12/16/2005  | B.R.        | 12/16/2005 | 6/28/2010  |
|                                                                                                                  | A3   |  <b>pui audio</b><br>a projects unlimited company inc |            |            | AWB-25R6-12 |             |            |            |
|                                                                                                                  |      |                                                                                                                                            |            |            | Siren       |             |            |            |
| AWB-25R6-12.idw                                                                                                  |      |                                                                                                                                            |            |            |             | -           | 1 / 1      |            |