
Item no.: 750-508
Product description: 2-CHANNEL DIGITAL OUTPUT MODULE DC 24 V 2.0 A /
DIAGN. POSITIVE SWITCHING SHORT-CIRCUIT
PROTECTED

Produkt kann von Bild abweichen / product may differ

Packing unit 10 10*1 pieces

RoHS compliant

No. of outputs	2
CURRENT CONSUMPTION (INTERNAL)	14 mA
Type of load	resistive, inductive, lamps
Max. switching frequency	1 kHz
Reverse voltage protection	Yes
Output current max.	2 A
Short-circuit range typ. Pwm	15 A / 2 s
Open-circuit detection	0.2 mA
Diagnostics	Open circuit-, overload- and short-circuit protection
Isolation	500 V system / supply
Current consumption typ (field side)	7 mA / MODULE + LOAD
Internal data width	2 Bit In, 2 Bit Out
Single current	2000 mA
Conformity marking	CE
Cross section [mm ²]	0.08 - 2.5 mm ²
Cross section [AWG]	28 - 14 AWG
Connection method	CAGE CLAMP® CONNECTION
Weight	50 g
Color	light gray
Height	64 mm
Height	2.52 in
Width	12 mm



Width	0.472 in
Depth	100 mm
Depth	3.937 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
Mounting	TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
750-508	ABS	03-HG374860/3-PDA			
750-508	BSH	Bescheinigung Nr. 467			
750-508	DNV	A-12306			
750-508	GL	26 898 - 05 HH			
750-508	IECEX	IECEX TUN 09.0001 X			
750-508	KR	HMB05880-AC002			
750-508	LR	02/20026 (E2)			
750-508	PRS	TE/1720/880590/08			
750-508	Rina	ELE153207CS001			
750-508	TÜV	TÜV 07 ATEX 554086 X			
750-508	UL	E175199 Sec.1			
750-508	UL	E198726 Sec.1			

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected