


# Farnell InOne Product Submission – Cooper B-Line

## Access Product Range



OR



### **Access 19" Free-standing Equipment Cabinet**

This unique cabinet innovation has been specifically designed to bring unrivalled advantages to free standing cabinets and will offer a number of benefits to ultimately **reduce the total cost of ownership**. The cabinet comprises of the basic Access frame with front and rear 19" mounting angles, side and top panels

- Totally open construction
- No corner posts – 360<sup>0</sup> accessibility
- Unrestricted top/base cable entry
- Stylish appearance blends elegance with functionality
- High security
- Quick release doors and side panels
- 3 door types available –vented glass, vented steel or plain steel
- 500Kg Load Capacity (evenly distributed)
- Supplied in flat pack form with instructions

Part Codes:

| Part No  | Description                             |
|----------|-----------------------------------------|
| A2766xxx | 27U cabinet, 600W, 600D                 |
| A2768xxx | 27U cabinet, 600W, 875D                 |
| A4266xxx | 42U cabinet, 600W, 600D                 |
| A4268xxx | 42U cabinet, 600W, 875D                 |
| A4288xxx | 42U cabinet, 800W, 875D                 |
| AGD276A  | Access Ventilated Glass Door, 27U, 600W |
| AGD426A  | Access Ventilated Glass Door, 42U, 600W |
| AGD428A  | Access Ventilated Glass Door, 42U, 800W |
| ASD276A  | Access Steel Door, 27U, 600W            |
| ASD426A  | Access Steel Door, 42U, 600W            |
| ASD428A  | Access Steel Door, 42U, 800W            |
| AVD276A  | Access Ventilated Steel Door, 27U, 600W |

|         |                                         |
|---------|-----------------------------------------|
| AVD426A | Access Ventilated Steel Door, 42U, 600W |
| AVD428A | Access Ventilated Steel Door, 42U, 800W |




### Access Server Cabinet

The Access Server cabinet is one of the most advanced Server cabinets available today. The design provides an exceptional system for housing both free standing and rack mounted servers from all common manufacturers. The cabinet is supplied with 2 fully ventilated steel doors, quick release side panels, ventilated top panels and a fully retractable stabilising plinth supplied with jacking feet.

- Front and rear 19" mounting angles
- Mounting angles are fully adjustable up to a mounting depth of 762mm between the front and rear angles
- Excellent ventilation throughout the cabinet with 53% open area door ventilation
- Stabilising plinth
- Supplied as flat pack

| Part No   | Description                     |
|-----------|---------------------------------|
| A4268xxxx | 42U Server Cabinet, 600W, 875D  |
| A4768xxxx | 42U Server Cabinet, 600W, 1000D |


## Cabinet Accessories



### Cable Tray

- A convenient adjustable vertical cable management solution that fits within the side depth area of any Access cabinet system
- Can be mounted in various positions in the side of an Access cabinet via two screws and cage nuts at the top and bottom
- 75mm version can also be used for front or rear vertical cable management on 800 wide Access cabinets
- Easily adjustable - trays can be conveniently positioned to allow cable runs to be positioned in the optimum location
- Two sizes (75mm wide and 150mm wide) to cope with majority of applications
- Supplied with full fitting instructions
- Supplied complete with fixings

| Part No | Description                |
|---------|----------------------------|
| ACTR27  | 27U Cable Tray, 75mm Wide  |
| ACTR42  | 42U Cable Tray, 75mm Wide  |
| ACTRW27 | 27U Cable Tray, 150mm Wide |
| ACTRW42 | 42U Cable Tray, 150mm Wide |



### Cable Basket

- A convenient adjustable vertical cable management solution that fits within the centre vertical extrusion of any Access Cabinet System
- The basket ensures that loads associated with high volume cabling are supported in an optimum manner
- The open structure of the cable basket offers enhanced cable management features and allows cables to be distributed and supported at all levels throughout the cabinet
- Two sizes (150mm wide and 300mm wide) to cope with majority of applications
- Zinc plate and clear passivate
- Supplied with full fitting instructions
- Supplied complete with fixings

| Part No | Description                  |
|---------|------------------------------|
| ABS2715 | 27U Cable Basket, 150mm Wide |

|         |                              |
|---------|------------------------------|
| ABS4215 | 42U Cable Basket, 150mm Wide |
| ABS2730 | 27U Cable Basket, 300mm Wide |
| ABS4230 | 42U Cable Basket, 300mm Wide |



### Plastic Cable Tidies

To Complement the unique Access open frame, two sizes of cable tidy are available which can be fitted to any Access Cabinet System

- Fits Directly To 19" Panel Mounts
- Single Hole Fixing
- Hinged Gate Clip Action
- Multiple Mounting Positions


| Part No | Description                           |
|---------|---------------------------------------|
| CTS     | Small Cable Tidy, 80mm x 40mm x 26mm  |
| CTL     | Large Cable Tidy, 120mm x 60mm x 28mm |



### Twist & Lock Cable Management

The new Twist and Lock cable management system is designed to fit on all Access Cabient 19" panel mounts. It provides a versatile system for vertical and horizontal cable management with the large diameter ensuring the correct bend radius on cables. The arms can be fitted at any increments of 2 'U' into location holes on the 19" panel mounts.

| Part No | Description                |
|---------|----------------------------|
| TLCMS   | Arms and ends (pack of 10) |
| TLCMR   | Divider rings (pack of 10) |



### Metal Cable Hoops

Vertical cable management is a common problem with conventional cabinet construction but with Access it is possible to fit cable hoops to the front or rear 19 inch uprights, within the 600mm overall width footprint, whilst still allowing front entry/exit of cables. This is particularly important when cabinets are bayed together. This new cable management solution provides a minimum cable area of 1550mm<sup>2</sup> on a 600mm wide rack rising to 6500mm<sup>2</sup> on 800mm wide cabinets.

| Part No | Description                              |
|---------|------------------------------------------|
| ACH6    | Cable hoop for 600 or 800mm wide cabinet |
| ACH8    | Cable hoop for 800 mm wide cabinet       |



### Jacking Feet

Level and stabilise cabinets on uneven floors.

### Castors

Each castor kit consists of 4 locking castors and hardware.



| Part No    | Description                                    |
|------------|------------------------------------------------|
| AJF-KIT-FN | Jacking feet (set of 4 with mounting hardware) |
| ACK-KIT-FN | Castors (set of 4 with mounting hardware)      |




### Plinth Kit

A plinth kit can be added to any Access Cabinet to provide easy access into the base of the cabinet.

Each kit comprises of 4 corner plates fitted with a jacking foot and castor, plus 4 'kick plates' to fill the gap between the cabinet and the floor

| Part No  | Description                           |
|----------|---------------------------------------|
| AMP66AFN | Plinth kit single cabinet 600 x 675mm |
| AMP68AFN | Plinth kit single cabinet 600 x 875mm |
| AMP88AFN | Plinth kit single cabinet 800 x 875mm |



### Stabilising Plinth Kit

The stabilising plinth includes a pull out section at the front to add extra stability to the cabinet when withdrawing heavy equipment on slides. Each kit also includes 4 corner plates fitted with a jacking foot and castor, plus 'kick plates' to fill the gap between the cabinet and the floor


| Part No   | Description                        |
|-----------|------------------------------------|
| SAMP66AFN | Stabilising plinth kit 600 x 675mm |
| SAMP68AFN | Stabilising plinth kit 600 x 875mm |
| SAMP88AFN | Stabilising plinth kit 800 x 875mm |



### Earth Kit

Provides earth continuity for any Access cabinet

| Part No | Description      |
|---------|------------------|
| AEK     | Access Earth Kit |



### Fan Trays

Where additional cooling is required, a fan tray can be added to the top of any Access Cabinet to assist natural convection within the cabinet

- Replaces vented or plain top panels.
- Simple 2 fastener fixing.
- Can be turned through 180°.

| Part No | Description                                  |
|---------|----------------------------------------------|
| ATP64A  | 2 Fan Tray Top Panel for 600W Cabinet 230VAC |
| ATP84A  | 2 Fan Tray Top Panel for 800W Cabinet 230VAC |



### In-Rack Ventilation Unit

Based on universal 19" mounting centres (IEC 297 standard), Cooper B-Line offer two sizes of In-Rack Ventilation Units. Both 3 and 6 fan versions share the same characteristics.

- Fits directly to panel mounts.
- Neon power indicator.
- Occupies only 1U of rack space.

| Part No | Description                          |
|---------|--------------------------------------|
| IVU3    | 1U 19" 3 Fan Ventilation Unit 230VAC |
| IVU6    | 1U 19" 6 Fan Ventilation Unit 230VAC |

## General cabinet and 19" Accessories



### Quick Fit Fixed Shelf for all Access Cabinets


This new range of shelves are designed for easy installation and can be fitted in a matter of minutes..

Features:

- 4 Depths: 450, 550, 650 and 750mm.
- Ventilated Shelf to assist convection.
- Unique Bracket requires no fixings.
- Simple thumb screw locks shelf in position.
- Add and remove shelves in seconds
- Designed for loads up to 35kg.

Description Depth Part No.

| Part No | Description           |
|---------|-----------------------|
| QRSV45  | 19" width 450mm depth |
| QRSV55  | 19" width 550mm depth |
| QRSV65  | 19" width 650mm depth |
| QRSV75  | 19" width 750mm depth |




### Universal Fit Sliding Shelf

To suit Access and any 19" Enclosures with Front & Rear IEC 19" Fixings

- Vented Shelf to Assist Convection
- Adjustable Rear Bracket – allows 19" rails to be moved independent of shelf depth
- Fits any 19" cabinet by utilising front and rear mountings
- Designed for loads up to 45kg (evenly distributed)

| Part No  | Description                                    |
|----------|------------------------------------------------|
| LDATSV45 | Adjusts between 444 – 749mm, shelf depth 455mm |
| LDATSV55 | Adjusts between 444 – 812mm, shelf depth 555mm |
| LDATSV70 | Adjusts between 444 – 940mm, shelf depth 705mm |



### Universal Quick Fit Sliding Shelf

To suit Access and any 19" Enclosures with Front & Rear IEC 19" Fixings

- Vented Shelf to Assist Convection
- Adjustable Rear Bracket
- Unique Fitting Requires No Tools
- Designed for loads up to 125Kg (evenly distributed)

| Part No | Description                                    |
|---------|------------------------------------------------|
| QRTSV45 | Adjusts between 363 - 513mm, Shelf depth 450mm |
| QRTSV60 | Adjusts between 513 - 663mm, Shelf depth 600mm |
| QRTSV75 | Adjusts between 663 - 813mm, Shelf depth 750mm |



### Sliding Keyboard Shelf

Enables a standard keyboard to be used any 19" cabinet. Turntable permits a keyboard which is wider than 450mm to be turned through 90° for storage. Universal mounting brackets fit uprights set between 450 & 750mm apart.

- Depth adjustable between 450 & 750mm
- Universal mounting fits any standard 19" cabinet

| Part No | Description            |
|---------|------------------------|
| KT750   | Sliding Keyboard Shelf |



### Cantilever (Modem) Shelves

Fits to front face of 19" mounting angles, with angles set at standard 19" width. Ideal for modems, hubs or other networking equipment.

| Part No | Description                                  |
|---------|----------------------------------------------|
| MS19    | 1U 19" Front Mounted Modem Shelf, 190mm deep |
| MS40    | 2U 19" Front Mounted Modem Shelf, 400mm deep |
|         |                                              |



### Magnetic Internal Lighting Unit

A compact internal fluorescent cabinet light with on/off switch and socket for additional equipment. Can be either mounted using the built in magnetic strip or screw fixed to standard 35mm DIN rail. 2.5mm<sup>2</sup> connectors for incoming power cable (not supplied)

| Part No | Description                   |
|---------|-------------------------------|
| KL02510 | Magnetic Light with UK socket |



### Unit Height Labels:

One of the most difficult tasks when fitting equipment in 19" cabinets is locating the unit height position for mounting. Cooper B Line have solved this problem by supplying a self adhesive 'U' height numbering strip which simply fixes to the front face of the 19" panel mounts.

- Pressure sensitive self adhesive.
- Universal size to suit all Access cabinets.
- Just trim to the desired unit height as required.
- Black lettering on white background.

| Part No | Description                                          |
|---------|------------------------------------------------------|
| AUHL    | Pairs of height labels, 1-47 - Top to Bottom         |
| AUHLR   | Pairs of height labels, 1-47 - Bottom to Top         |
| AUHLFR  | Pairs of height labels, 1-47 & 48-94 - Top to Bottom |



### Jumper Ring Panels

To compliment the unique Access open frame, effective horizontal cable management remains a necessary element of any cabling system. Based on universal 19" mounting centres (IEC 297 standard), the 1 and 2 U high panels have welded cable support hoops.

#### Features:

- Fits Directly To 19" Panel Mounts
- Four Cable Loops Per Panel
- Fits directly onto Cooper B-Line's Access 19-inch mounting angle

| Part No | Description          |
|---------|----------------------|
| JRP1    | 1U Jumper Ring Panel |
| JRP2    | 2U Jumper Ring Panel |