

PATCHCORDS/MOLDED CABLES

Audio and Video Patchcord, and Molded Cables Series 1/4", Mil-Type, TT or Bantam, Video Series

39

Ordering Information

Part Number	Type	Plug Finger	Description
Audio Patchcords			
18QD18	1/4" Mil-Type	Brass	2 foot, black nylon jacket
18QF18	1/4" Mil-Type	Brass	3 foot, black nylon jacket
18QH18	1/4" Mil-Type	Brass	4 foot, black nylon jacket
20QD20N*	1/4" Mil-Type	Nickel	2 foot, nylon jacket
20QF20N*	1/4" Mil-Type	Nickel	3 foot, nylon jacket
20QH20N*	1/4" Mil-Type	Nickel	4 foot, nylon jacket Uses 2 cond. shielded cable
TT122	TT or Bantam	Brass	1 foot, molded gray jacket
TT124	TT or Bantam	Brass	2 foot, molded gray jacket
TT126	TT or Bantam	Brass	3 foot, molded gray jacket
TT127	TT or Bantam	Brass	4 foot, molded gray jacket
TT128	TT or Bantam	Brass	5 foot, molded gray jacket
TT122N*	TT or Bantam	Nickel	1 foot, molded
TT124N*	TT or Bantam	Nickel	2 foot, molded
TT126N*	TT or Bantam	Nickel	3 foot, molded
TT127N*	TT or Bantam	Nickel	4 foot, molded
TT128N*	TT or Bantam	Nickel	5 foot, molded
TT742N*	TT or Bantam	Nickel	1 foot, nylon jacket
TT744N*	TT or Bantam	Nickel	2 foot, nylon jacket
TT746N*	TT or Bantam	Nickel	3 foot, nylon jacket
TT747N*	TT or Bantam	Nickel	4 foot, nylon jacket Uses 2 cond. shielded cable
Digital AES/EBU Patchcords			
DTT122	TT or Bantam	Nickel	1 foot, 110 Ohm, black, molded
DTT124	TT or Bantam	Nickel	2 foot, 110 Ohm, black, molded
DTT126	TT or Bantam	Nickel	3 foot, 110 Ohm, black, molded
DTT128	TT or Bantam	Nickel	5 foot, 110 Ohm, black, molded
DTT133	TT or Bantam	Nickel	10 foot, 110 Ohm, black, molded
DMT122	1/4" Mil-Type	Nickel	1 foot, 110 Ohm, black
DMT124	1/4" Mil-Type	Nickel	2 foot, 110 Ohm, black
DMT126	1/4" Mil-Type	Nickel	3 foot, 110 Ohm, black
DMT128	1/4" Mil-Type	Nickel	5 foot, 110 Ohm, black Uses 2 cond. shielded, 110 Ohm cable

Ordering Information

Part No.	Description
Molded MIDI Cables	
MD3	3 foot, 5 pin DIN, molded black
MD6	6 foot, 5 pin DIN, molded black
MD10	10 foot, 5 pin DIN, molded black
MD15	15 foot, 5 pin DIN, molded black Uses 4 cond., 24 awg, PVC outer jacket, braided shielded cable
1/4" Cables	
05AD05	2 foot, mono, male to male
05AK05	6 foot, mono, male to male
05AN05	10 foot, mono, male to male
05AU05	25 foot, mono, male to male
05AN15	10 foot, mono, male to RA male
05AN80	10 foot, mono, male to female
05AU80	25 foot, mono, male to female
10BF10	3 foot, stereo, male to male
10BK10	6 foot, stereo, male to male
10BN10	10 foot, stereo, male to male
15AK15	6 foot, mono, RA male to RA male
RCA	
25AF25	3 foot, male to male
25AK25	6 foot, male to male
25AN25	10 foot, male to male
25AK82	6 foot, male to female
30AK30	6 foot, RA male to RA male
30AN30	10 foot, RA male to RA male
30AR30	15 foot, RA male to RA male
1/4" to RCA	
05AK25	6 foot, 1/4" male to RCA male
05AN25	10 foot, 1/4" male to RCA male Uses either single or 2 cond, 22awg, PVC outer jacket, braided shielded cable

* When ordering, add the following for cable color: 0 - Black; 2 - Red; 5 - Green; 6 - Blue