


Coaxial Connectors and Crimping Tools



BNC PC Board/Panel Mount Jacks



| Right Angle (Max. Panel Thickness .240") 50 Ohm |            |           |            |                |                        | EACH |       |         |
|-------------------------------------------------|------------|-----------|------------|----------------|------------------------|------|-------|---------|
| Stock No.                                       | Mr.'s Type | Mfg. Hgt. | Body       | Mounting Posts | Center Contact Plating | 1-24 | 25-99 | 100-499 |
| 512-2171                                        | 226990-1   | 0.625"    | Wht. Valox | No             | Tin                    | 2.26 | 2.04  | 1.70    |
| 512-2172                                        | 226990-3   | 0.625"    | Wht. Valox | No             | Gold                   | 1.94 | 1.74  | 1.45    |
| 512-2173                                        | 227161-1   | 0.625"    | Wht. Valox | Yes            | Tin                    | 1.67 | 1.50  | 1.25    |
| 512-2174                                        | 227161-3   | 0.625"    | Wht. Valox | Yes            | Gold                   | 1.67 | 1.50  | 1.25    |
| 512-2176                                        | 227161-7   | 0.519"    | Wht. Valox | Yes            | Gold                   | 1.67 | 1.50  | 1.25    |
| 512-2175                                        | 226990-2   | 0.625"    | Blk. Valox | No             | Tin                    | 1.94 | 1.74  | 1.45    |
| 512-2178                                        | 226990-6   | 0.625"    | Blk. Valox | No             | Gold                   | 1.94 | 1.74  | 1.45    |
| 512-2177                                        | 227161-2   | 0.625"    | Blk. Valox | Yes            | Tin                    | 1.67 | 1.50  | 1.25    |
| 512-2180                                        | 227161-6   | 0.625"    | Blk. Valox | Yes            | Gold                   | 1.88 | 1.50  | 1.25    |
| 512-2179                                        | 227161-9   | 0.519"    | Blk. Valox | Yes            | Gold                   | 1.88 | 1.50  | 1.25    |
| 512-2181                                        | 227433-1   | 0.625"    | Metal      | No             | Tin                    | 4.44 | 4.00  | 3.33    |
| 512-2182                                        | 227676-1   | 0.625"    | Metal      | No             | Gold                   | 2.31 | 2.08  | 1.73    |
| 512-2183                                        | 227661-1   | 0.625"    | Metal      | Yes            | Tin                    | 2.25 | 2.03  | 1.69    |
| 512-2184                                        | 227677-1   | 0.625"    | Metal      | Yes            | Gold                   | 2.25 | 2.03  | 1.69    |

| Vertical (Max. Panel Thickness .240") 50 Ohm |          |        |            |     |      | 1-24 | 25-99 | 100-499 |
|----------------------------------------------|----------|--------|------------|-----|------|------|-------|---------|
| 512-2185                                     | 226993-1 | 1.375" | Wht. Valox | No  | Tin  | 4.44 | 4.00  | 3.33    |
| 512-2187                                     | 226993-3 | 1.375" | Wht. Valox | No  | Gold | 4.44 | 4.00  | 3.33    |
| 512-2189                                     | 227222-1 | 1.375" | Wht. Valox | Yes | Tin  | 1.82 | 1.63  | 1.36    |
| 512-2186                                     | 227222-3 | 1.375" | Wht. Valox | Yes | Gold | 1.67 | 1.50  | 1.25    |
| 512-2193                                     | 227222-6 | 1.375" | Blk. Valox | Yes | Gold | 2.13 | 1.92  | 1.60    |
| 512-2195                                     | 227671-1 | 1.375" | Metal      | Yes | Tin  | 2.13 | 1.94  | 1.60    |
| 512-2188                                     | 227673-1 | 1.375" | Metal      | Yes | Gold | 1.92 | 1.73  | 1.44    |

| Hardware  |             |             |      |         |         |
|-----------|-------------|-------------|------|---------|---------|
| Stock No. | Mfr.'s Type | Description | EACH |         |         |
|           |             |             | 1-99 | 100-499 | 500-999 |
| 512-2190  | 1-329632-2  | Lock Washer | .15  | .13     | .12     |
| 512-2191  | 1-329631-2  | Jam Nut     | .17  | .15     | .14     |

Twin BNC Connectors



Plugs — Fig. A

| Stock No. | Mr.'s Type | For RG/U Cable | Contact Plating | Body Plating | Dielectric | CERTI-CRIMP™ Hand Tool | EACH  |       |       |
|-----------|------------|----------------|-----------------|--------------|------------|------------------------|-------|-------|-------|
|           |            |                |                 |              |            |                        | 1-24  | 25-49 | 50-99 |
| 512-2340  | 332225     | 108, 108A      | S               | S            | T          | 69667                  | 16.48 | 14.83 | 12.36 |
| 512-2342  | 332225-5   | 108, 108A      | S               | N            | PP         | 69667                  | 13.61 | 12.38 | 11.24 |


| Bulkhead Jack — Fig. B |        |           |   |   |    |       |  | 22.17 | 19.95 | 16.63 |
|------------------------|--------|-----------|---|---|----|-------|--|-------|-------|-------|
| 512-2154               | 332342 | 108, 108A | S | N | PP | 69667 |  |       |       |       |

| Right-Angle PC Board/Panel Mount Jacks — Fig. C |             |               |                |      |       |       |
|-------------------------------------------------|-------------|---------------|----------------|------|-------|-------|
| Stock No.                                       | Mfr.'s Type | Body Material | Mounting Posts | EACH |       |       |
|                                                 |             |               |                | 1-24 | 25-49 | 50-99 |
| 512-2344                                        | 228686-1    | Wht. Valox    | Yes            | 6.80 | 6.12  | 5.10  |

| Bulkhead Jack Adapter — Fig. D |             |                 |              |       |       |       |
|--------------------------------|-------------|-----------------|--------------|-------|-------|-------|
| Stock No.                      | Mfr.'s Type | Contact Plating | Body Plating | EACH  |       |       |
|                                |             |                 |              | 1-24  | 25-49 | 50-99 |
| 512-2346                       | 332215      | S               | N            | 20.60 | 18.54 | 15.45 |

50 Ohm N Connectors

MIL-C-39012, Class 11, Category B qualified. Working voltage 1000 volt, RMS at sea level. Frequency Range: 0-11 GHz. Crimp Type: D.



| Crimp Plugs |            |                   |                 |              |            |            |                        | EACH  |       |       |
|-------------|------------|-------------------|-----------------|--------------|------------|------------|------------------------|-------|-------|-------|
| Stock No.   | Mr.'s Type | For RG/U Cable    | Contact Plating | Body Plating | Dielectric | Style      | CERTI-CRIMP™ Hand Tool | 1-24  | 25-49 | 50-99 |
| 512-2236    | 1-225661-2 | 58, 58A, 58B, 58C | G               | N            | T          | Mil type   | 220045-2               | 10.68 | 9.51  | 7.85  |
| 512-2238    | 225361-1   | 58, 58A, 58B, 58C | G               | S            | T          | Mil type   | 220045-2               | 22.81 | 20.73 | 19.01 |
| 512-2241    | 225661-2   | 8, 8A, 213        | G               | N            | T          | Mil type   | 220015-1               | 10.47 | 9.42  | 7.85  |
| 512-2242    | 1-227086-0 | 8, 8A, 213        | G               | N            | T          | Commercial | 220015-1               | 8.12  | 7.38  | 6.77  |
| 512-2248    | 225661-1   | 9, 9A, 9B, 214    | G               | N            | T          | Mil type   | 220015-1               | 18.40 | 16.73 | 15.33 |

Same Day Shipments For Product In Stock

SHV Connectors



Safe-tested at 5000 volts DC. Looks like, but isn't intermateable with other bayonet-type connectors. Comply with Bureau of Standard's specification ND-545. Polarized center contacts that are recessed in the dielectric. Crimp Type: D.

| Crimp Plugs |             |                   |                 |              |            |                        |       |       |       |
|-------------|-------------|-------------------|-----------------|--------------|------------|------------------------|-------|-------|-------|
| Stock No.   | Mfr.'s Type | For RG/U Cable    | Contact Plating | Body Plating | Dielectric | CERTI-CRIMP™ Hand Tool | EACH  |       |       |
|             |             |                   |                 |              |            |                        | 1-24  | 25-49 | 50-99 |
| 512-2254    | 51426-4     | 58, 58A, 58B, 58C | G               | N            | T          | 220022-1               | 16.50 | 15.00 | 13.62 |
| 512-2256    | 51426-2     | *                 | G               | S            | T          | 220022-2               | 19.47 | 17.52 | 14.60 |

\*59, 59A, 59B, 62, 62A, 62B, 124, 140, 210 Belden 9291, 9209, 9268.

| Bulkhead Solder Jacks |             |                 |              |            |       |       |       |
|-----------------------|-------------|-----------------|--------------|------------|-------|-------|-------|
| Stock No.             | Mfr.'s Type | Contact Plating | Body Plating | Dielectric | EACH  |       |       |
|                       |             |                 |              |            | 1-24  | 25-49 | 50-99 |
| 512-2260              | 51494-1     | G               | S            | T          | 12.60 | 11.34 | 9.45  |
| 512-2262              | 51494-2     | G               | N            | T          | 9.70  | 8.73  | 7.28  |

Miniature UHF Connectors



Rated for 335 volts rms at sea level .0 to 2.0 GHz frequency range. Crimp Type: D.

| Crimp Plug |             |                   |                 |              |            |                        |      |       |         |
|------------|-------------|-------------------|-----------------|--------------|------------|------------------------|------|-------|---------|
| Stock No.  | Mir.'s Type | For RG/U Cable    | Contact Plating | Body Plating | Dielectric | CERTI-CRIMP® Hand Tool | EACH |       |         |
|            |             |                   |                 |              |            |                        | 1-24 | 25-99 | 100-499 |
| 512-2264   | 226600-1    | 58, 58A, 58B, 58C | T               | N            | PP         | 220149-1               | .69  | .62   | .52     |

| Crimp Jack |          |                   |   |   |    |          |  | 2.70 | 2.43 | 2.03 |
|------------|----------|-------------------|---|---|----|----------|--|------|------|------|
| 512-2266   | 226602-1 | 58, 58A, 58B, 58C | T | N | PP | 220149-1 |  |      |      |      |

CERTI-CRIMP™ Hand Tools



AMP's finest tools. The CERTI-CRIMP™ ratchet is designed to provide a complete crimp cycle.

|                         |      |        |
|-------------------------|------|--------|
| 512-2400. 69140-1.....  | EACH | 542.64 |
| 512-2401. 69141-1.....  | EACH | 542.64 |
| 512-2402. 69245-1.....  | EACH | 520.88 |
| 512-2407. 69477-1.....  | EACH | 264.33 |
| 512-2409. 69477-2.....  | EACH | 276.05 |
| 512-2406. 69478-1.....  | EACH | 256.63 |
| 512-2133. 69667.....    | EACH | 764.32 |
| 512-2408. 220009-1..... | EACH | 284.38 |
| 512-2415. 220009-5..... | EACH | 435.20 |
| 512-2414. 220015-1..... | EACH | 770.13 |
| 512-2131. 220022-2..... | EACH | 399.84 |
| 512-2410. 220043-1..... | EACH | 353.04 |
| 512-2126. 220045-2..... | EACH | 428.65 |
| 512-2418. 220061-1..... | EACH | 506.33 |
| 512-2416. 220187-1..... | EACH | 234.44 |

PRO-CRIMPER™ II Hand Tools



Inexpensive and features interchangeable dies. Ratchet control for complete crimping cycle. Precision construction of durable high-carbon steel.

|                                                                          |      |       |
|--------------------------------------------------------------------------|------|-------|
| Type 58433-1. For "O" crimp plugs and jacks on RG58, 59, and 62 cables.  | EACH | 89.61 |
| 512-2380. 58433-1.....                                                   |      |       |
| Type 58433-2. For hex crimp plugs and jacks on RG-58, 59, and 62 cables. | EACH | 96.51 |
| 512-2381. 58433-2.....                                                   |      |       |

ALLIED ► 413