


IEC 947-5-1 ELECTRICAL RATING													
SILVER CONTACTS						GOLD PLATED CONTACTS		ENVIRONMENTAL		APPROVALS			
AC		AC (FOR ZNC)		DC		$I_{th} = 10A$ 1V 10μA MIN. 50V 100mA MAX.		IP66 NEMA 1, 4, 12, 13		  IEC 947-5-1 EN50047			
A600 U _e	AC15 I _e	A500 U _e	AC15 I _e	O300 U _e	DC13 I _e			TEMP RANGE :	-25°C TO 85°C -13°F TO 185°F				
VOLTS	AMPS	VOLTS	AMPS	VOLTS	AMPS			STORAGE :	-40°C TO 85°C -40°F TO 185°F				
120	6	120	6	125	0.55		SHOCK : 50G PER IEC 68-2-27 VIBRATION : 10G PER IEC 68-2-6						
240	3	240	3	250	0.27								
480	1.5	380	1.5										
500	1.4	480	1.4										
600	1.2												
THE COPYRIGHT OF THIS DRAWING IS THE PROPERTY OF HONEYWELL LTD. THE DRAWING IS SUPPLIED IN CONFIDENTIAL AND NOT TO BE USED FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT IS SUPPLIED.						THIRD ANGLE PROJECTION		SCALE 1:1		DIMENSIONS ARE IN MM/INCHES.		MODIFY ON CAD SYSTEM ONLY	



NOTE:
FOR CONNECTION DIAGRAMS AND ADDITIONAL
ELECTRICAL, ENVIRONMENTAL & DIMENSIONAL
INFORMATION SEE DRAWING GL-49212.