








5215 Pos.

NOTES:

1. MATERIAL: HOUSING - NYLON 66 (UL94V-0)
POST - TIN BRASS

2. APPLICABLE RECEPTACLE P/N 173977

3. THIS PART HAS BEEN OBSOLETE.



RECOMMENDABLE PCB LAYOUT
(PCB THK:0.8-1.6)

THIS DRAWING IS A CONTROLLED DOCUMENT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DMN	31JAN03
		S.XU	
		CHK	31JAN03
		S.YAO	
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APRO	31JAN03
MM		T. SASAKI	
		NAME	
		POST HEADER ASS'Y HORIZONTAL TYPE	
		 Tyco Electronics Corporation SHANGHAI, CHINA	

7-292253-5	5-292253-5	5-292253-5	1-292253-5	15	28	31.8	26.2	31.0
7-	4	5-	4	3-	4	1-	4	
7-	-3	5-	-3	3-	-3	1-	-3	13
7-	-2	5-	-2	3-	-2	1-	-2	12
7-	-1	5-	-1	3-	-1	1-	-1	11
7-	-0	5-	-0	3-	-0	1-	-0	10
6-	-9	4-	-9	2-	-9		-9	9
6-	-8	4-	-8	2-	-8		-8	8
6-	-7	4-	-7	2-	-7		-7	7
6-	-6	4-	-6	2-	-6		-6	6
6-	-5	4-	-5	2-	-5		-5	5
6- 	-4	4-	-4	2-	-4		-4	4
6-	-3	4-	-3	2-	-3		-3	3
6-292253-2	4-292253-2	2-292253-2	292253-2	2	2	5.8	—	5.0
BLACK	YELLOW	BLUE	NATURAL	Pos.	A	B	C	D

TOLERANCES UNLESS OTHERWISE SPECIFIED:	
10 >=	* ±0.2
30 >=	* >10 : ±0.25
100 >=	* >30 : ±0.3
ANGLE	: ±3°

	2 P/LC 3 P/LC 4 P/C	± - ± - ± - ± -
MATERIAL SEE NOTE	FINISH ANGLES	SEE NOTE

108-B0010						
APPLICATION SPEC						
—	SIZE	CAGE CODE	DRAWING NO			RESTRICTED TO
WEIGHT		A3	00779	C-292253		—
—						
CUSTOMER DRAWING				SCALE	5.1	SHEET 1 OF 1
						REV A