

Model 6733, 6734
Test Lead Wire with Silicone or PVC Insulation**Features**

- Same wire as used with the Pomona test leads and patch cords.
- Make your own “Extra Long” test leads, jumpers or patch cords.
- Fits Pomona “Do-It-Yourself” banana plugs and jacks.
- High temperature and voltage ratings.
- Silicone insulation with high wire strand count allows for superb flexibility.
- Wear indication with double insulated (dual extruded) silicone leads shows white inner layer for increased safety.
- Wire will comply with International Safety Standard CAT III, IEC61010-031 requirements when correctly terminated with other components designed to meet CAT III, IEC61010-031 requirements.



Specifications:	6733	6734
Insulation:	Silicone	PVC
Length:	50 FT (15,2 meters)	50 FT (15,2 meters)
Wire size:	18 AWG	18 AWG
Wire:	192 X 41 bare copper	65 X 36 tinned copper
Diameter (OD):	.144" (3,60mm)	.144" (3,60mm)
Temperature:	-58° to +302°F (-50° to +150°C)	-4° to +221°F (-20° to +105°C)
Wire Rated Voltage:	10,000 DC *	5,000 DC *
Current:	20 A	15 A
Ordering Information:		
Black Wire:	6733-0	6734-0
Red Wire:	6733-2	6734-2
* Hands free testing in controlled voltage environment: <i>For CE compliance:</i> not intended for hand held use at voltages above 30 Vrms / 42.2 Vpk / 60 Vdc or when current exceeds 8A maximum.		

USA: Sales: 800-490-2361
Technical Support: technicalsupport@pomonatest.com
Fax: 425-446-5844
Europe: 31-(0) 40 2675 150 **International:** 425-446-5500
Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.