

A fully screened robust range of DIN connectors for use in instrumentation and audio applications. Available in two finishes; bright nickel and non-reflective electrically conductive matt black. Robust construction incorporating cable grip and strain relief.


MATERIALS
HOUSING

- MOULDING
CONTACTS
- CABLE CLAMP
- GROMMET
- : Zinc Alloy, sprayed
with matt black
conductive paint
- : Nylon
- : Brass
- Silver Plated
- : Mild Steel
zinc plated
- : Black P.V.C.

ELECTRICAL RATINGS

- Working Voltage
- Test Voltage
- Insulation Resist.
- Current Rating
- Contact Resist.
- Capacity (mated)
- Temp. Range
- 100 Vd.c. or a.c. peak
- 1000 Vd.c.
- 10¹¹Ω min at 100 Vd.c.
- 4 A
- 10 mΩ max
- 3 pF
- 25°C to +70°C

Dimensions



Type	Deltron No
3 Way	591-0300
4 Way	591-0400
4 Way Switched	591-0410
5 Way 45°	591-0500
5 Way 60°	591-0510
5 Way Dice	591-0520
6 Way	591-0600
7 Way	591-0700
8 Way	591-0800

CONVERTED FROM PS0483 ISS4 (08.07.96) IN JAN 2003

DrgnNo 591 SERIES TITLE SCREENED DIN CONNECTOR LOCKABLE PLUG (BLACK) ALL DIMENSIONS IN MM ANGLES IN DECIMAL DEGREES

DELTRON Components

ISS 4

GENERAL SPECIFICATION
FOR 591 SERIES

CUSTOMER

Aprvd Date 10/02/03

Aprvd By

MC

Drwn by BFS

Scale: NTS

Sheet 1 / 1