

PFBRCBLA -- FRPT Flush Duplex Series



Replacement cover for one-piece and two-piece flush poke-throughs featured on the previous page. Insert cover only, excludes carpet flange and receptacle.

Product Specifications

Product Type	
Flush Duplex Offering	Replacement Covers
Color	
Complies with:	UL 514A requirements for scrub water protection.
Fire Rating	For use in 1, 1 1/2, 2, 3 or 4 hour rated unprotected reinforced concrete floors or in 1, 2 or 3 hour rated floors employing steel floor units and concrete topping (D900 series design).
Floor Thickness Range	2 1/4" (over metal deck) to 7" (57.2 to 117.8)
UL Installation Spacing	Minimum of 2 feet on centers and not more than one unit per 65 sq. ft. of floor area in each span.
Cored Hole	3" (76.2) diameter
Receptacles	Hubbell #HBL5352, NEMA 5-20R; 20A, 125V AC
Jack(s)	Low Voltage Knockout Only.
Device and Cover Flap Material	Thermoplastic
Carpet Flange Material	Painted Cast Aluminum/Solid Brass, Brushed and Laquered.
Listings	UL Listed, CSA Certified
Housing	Engineered flame-retardant thermoplastic UL rated 94V-0
UPC Number	78358534256
Weight in LBs	0.3
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog

