






- ① HOUSING MATERIAL: LIQUID CRYSTAL POLYMER PER ASTM D5138 LCP000 G30A 32250.
- ② CONTACT MATERIAL: PHOSPHOR BRONZE.
- ③ CONTACT FINISH:
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL.
ON MATING SURFACES:
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA
UNCONTROLLED ENVIRONMENT.
ON LEADS
0.00381 MIN TIN-LEAD OVER UNDERPLATE.
LUBRICATION (ENTIRE CONTACT):
SURFACE CONDITIONER PER AMP SPEC 112-1002 AFTER PLATING.
- ④ PART MARKING PER AMP INCORPORATED SPECIFICATION 115-9009, LOCATED
APPROXIMATELY AS SHOWN.
- ⑤ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



	4.25	6.5	34	17	35.88		72	1-536501-1
 OBSOLETE	4.25	6.5	130	65	131.88		264	1-536501-0
	4.25	6.5	106	53	107.88		216	536501-9
	4.25	6.5	118	59	119.88		240	536501-8
	4.25	6.5	82	41	83.88		168	536501-7
OBSOLETE	4.25	6.5	58	29	59.88		120	536501-6
	4.25	6.5	70	35	71.88		144	536501-5
	4.25	6.5	94	47	95.88		192	536501-4
	4.25	6.5	46	23	47.88		96	536501-3
	4.25	6.5	22	11	23.88		48	536501-2
	4.25	6.5	10	5	11.88		24	536501-1
		E	D	C	B	A	FINISH	NO OF POSN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.R.BENDER 08/06/92		 TE Connectivity	
		CHK R.BENDORF 09/14/92			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm				Z-PACK 2mm FB, SIGNAL MODULE, PIN ASSEMBLY	
		APVD R.BENDORF 09/14/92		PRODUCT SPEC	
		—		2mm	
		APPLICATION SPEC		—	
		—		—	
MATERIAL	FINISH	WEIGHT	—	SIZE	—
		A1		CAGE CODE	00779
		DRAWING NO		C=536501	
		CUSTOMER DRAWING		RESTRICTED TO	
				—	
				SCALE 4:1	
				SHEET 1 of 1	
				REV S	