

18FF- 4Z- C5

RELAY SOCKET



CHARACTERISTICS



Ambient temperature :	-40 °C to 70°C
Rated voltage:	300VAC
Rated current :	12A (per pole)
Insulation voltage (Min.) :	5000VAC
Protection degree DIN40050 :	IP20
Socket material :	PA66+GF V0 (UL)
Contacts spring material :	QSn6.5-0.1
Plastic retainer :	available
White plastic tag :	available
Modules (on request) :	HFAA to HFHU module available
Terminal torque :	0.6Nm
Wire strip length :	7mm

Applicable relay type: HF18FF (JZX-18FF) (4 poles)

DIMENSIONS, PC BOARD LAYOUT AND WIRING DIAGRAM


Unit: mm

Outline Dimensions




(Top View)

Wiring Diagram



(Top View)

Retainer Dimensions



HONGFA RELAY

ISO9001、ISO/TS16949、ISO14001、OHSAS18001 CERTIFIED

2007 Rev. 1.00