



(0,80 mm) .0315"

QRM8-078-05.0-L-D-A

QRM8-036-05.0-L-D-DP-A-K

QRM8-026-02.0-L-D-A

QRM8 SERIES

SLIM BODY GROUND PLANE HEADER

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?QRM8

Insulator Material:

Black LCP

Terminal & Ground Plane Material:

Phosphor Bronze

Plating:

Au or Sn over

50µ" (1,27 µm) Ni

Current Rating:

Contact:

2.2 A per pin

(1 pin powered per row)

Ground:

8.5 A per ground plane

(1 ground plane powered)

Operating Temp Range:

-55°C to +125°C

Voltage Rating:

215 VAC

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0,10 mm) .004" max (018-026)

(0,15 mm) .006" max (036-078)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



FILE NO. E111594

ALSO AVAILABLE (MOQ Required)

- Other platings
- Contact Samtec.

MATED HEIGHT*

QRM8 LEAD STYLE	QRF8 LEAD STYLE	
	-05.0	-07.0
-02.0	(7,00) .276	(9,00) .354
-05.0	(10,00) .394	(12,00) .472
-07.0	(12,00) .472	(14,00) .551

*Processing conditions will affect mated height.

Note: Patented

Note: Some lengths, styles and options are non-standard, non-returnable.

Board Mates:

QRF8

Cable Mates:

EQRD



10 year Mixed Flowing Gas with 30µ" Gold
Call Samtec for maximum mated cycles

Increased wipe for rugged applications

Integral ground/power plane

Choice of stack heights

(1,20 mm)
.047" NOMINAL
WIPE

Protocols Supported


100 GbE

Download app notes at
www.samtec.com/appnote
Contact SIG @ samtec.com
for questions on protocols

Finalinch
CERTIFIED

28+
Gbps

QRM8	PINS PER ROW NO. OF PAIRS	LEAD STYLE	PLATING OPTION	TYPE	A	OTHER OPTION
	-026, -052, -078 (52 total pins per bank = -D)	-02.0 = 2 mm Body Height (Not available with -054 & -078 positions)	-L = 10µ" (0,25 µm) Gold on contact, Matte Tin on tail	-D = Single-Ended		-GP = Guide Post (Requires -GP on mating connector)
	-018, -036, -054 (18 pairs per bank = -D-DP)	-05.0 = 5 mm Body Height		-D-DP = Differential Pair		-K = (5,00 mm) .197" DIA Polyimide Film Pick & Place Pad
		-07.0 = 7 mm Body Height				-TR = Tape & Reel (-018, -026, -036, -052 only)



LEAD STYLE	A	B
-02.0	(4,81) .189	(6,12) .241
-05.0	(7,81) .307	(9,12) .359
-07.0	(9,78) .385	(11,12) .438



- Edge Rate® contacts
- Increased contact wipe
- 10 year MFG
- Guide post option