


DO NOT
SCALE FROM
THIS PRINT

EMF-1XX-XX-XX-D

No OF POSITIONS
-05 THRU -50
(PER ROW)

LEAD STYLE

-01 EDGE MOUNT (.031")
*-02: EDGE MOUNT (.062)

BODY SPECIFICATION

-D: DOUBLE
(USE SFM-XX-D-EM-XX)




PLATING SPECIFICATION

-F: 3μ " SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL.
-L: 10μ " SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL.
-S: 30μ " SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL.
-T: MATTE TIN ON CONTACT AND TAIL.
-FM: 3μ " SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL.
-LM: 10μ " SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL.
-SM: 30μ " SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL.

* =NOT RELEASED FOR PRODUCTION

TABLE 4

LEAD STYLE	BODY	CONTACT	"A"
-01	SFM-XX-D-EM-01	C-61-06-X	.126 [3.20]
*-02	SFM-XX-D-EM-02	C-61-08-X	.105 [2.67]

SECTION "A"-"A"
SCALE 4 : 1

PACKAGING VIEW

NOTES:

1. C1 REPRESENTS A CRITICAL DIMENSION.
2. MINIMUM PUSHOUT FORCE: .5 LB
3. ALL POSITIONS TO BE PACKAGED IN TUBES.

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:

DECIMALS ANGLES
.XX: $\pm .01 [.3]$ 2°
.XXX: $\pm .005 [.13]$
.XXXX: $\pm .0020 [.051]$

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 3:1

INSULATOR: LCP, UL 94 VO, COLOR BLACK

TERMINAL: BeCu, 1/2 HARD, AGE HARDENED

F:\dwg\MISC\Mktg\EMF-1XX-XX-XX-D-MKT.SLDDRW

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 53322

DESCRIPTION:

.050 X .050 EDGE MOUNT SOCKET STRIP DUAL ROW ASSEMBLY

DWG. NO.

EMF-1XX-XX-XX-D

BY: PURVIS

7-26-96

SHEET 1 OF 1