



Dimensions: In.

■ Specifications:

- Primary voltage: 115VAC 60Hz
- Primary exciting current: 90mA (max.)
- Secondary voltage (no load): 26.8CT VAC \pm 0.8V%
- Secondary voltage (full load): 24.0CT VAC \pm 0.8V%
- Rated secondary current: 1.0A (AC) 60Hz
- Voltage regulation: $< 15\% (VNL - VFL) / (VFL) \times 100$
- Temperature rise (@ room temp. 25°C): $< 70^\circ\text{C}$
- Breakdown voltage (HiPOT): 2000VAC 60Hz for 1 minute
- Coil to coil insulation: 200M Ω (min.) 500VDC
- Strain relief: 10 lbs
- Tinned lead length: 10mm
- Crossover insulation: 0.05mm polyester tape

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

41FK010