

Heavy-Duty Power Extension Cord, 15A, 14AWG (IEC-320-C14 to IEC-320-C13), 18-in.

MODEL NUMBER: **P005-18N**



Highlights

- C13 to C14 Power Cable, 1.5-ft. (18 in.)
- 14 AWG x 3C
- 15A / 100 - 250V
- RoHS Compliant
- UL Listed

Package Includes

- C13 to C14 Power Cable, 1.5-ft. (18 in.)

Description

Use Tripp Lite's P005-18N in server applications that require a high-rated, heavy-gauge cable. Its short length is perfect for server to PDU or UPS connections that are in close proximity. C13 to C14 connectors, 3 x 14 AWG conductors, 15A rating and 100-250V.

Features

- Short length reduces rack cable clutter
- Molded, heavy-duty power cable, 1.5-ft. (18 in.)
- IEC-320-C13 to IEC-320-C14
- 14 AWG x 3C, SJT, 15A, 100-250 Volt
- RoHS Compliant
- UL Listed

Specifications

General Info	
Product Group	POWER CORDS
OVERVIEW	
Intended Application	Powering Devices
Cable Type	POWER
Model Type	Power Cords
INPUT	
Cable Length (ft.)	1.5



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (m)	0.46
Cable Length (in.)	18
UPC ASSIGNMENT	
Unit Carton UPC#	037332155931
PHYSICAL	
Color	Black
Style	Power Cables
CONNECTIONS	
Connector A	IEC-320-C14
Connector B	IEC-320-C13
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.