









- NOTES:
1. DIMENSIONS IN PARENTHESES ARE IN METRIC.
 2. COLOR: LIGHT GREY
 3. "T" DIMENSION IS REFERENCE ONLY.
 4. MOUNTING HOLE SLOT DIMENSIONS: .16 (4.0) X .31 (8.0) - TYP.
 5. NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH THE RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE DUCTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.
 6. ONE COMPLETE MOUNTING HOLE ON BOTH ENDS OF DUCT WILL NOT BE COVERED BY TAPE.



H FL50X50LG-A 2 STRIPS OF TAPE
J FL12X12LG-A & FL25X25LG-A TAPE CENTERED

CAD FILENAME/LAYERS D38086BC_DC_FL50X50_00G.prt

--	-----	---	---	K. ADDED NOTE ABOUT TAPE LOCATION				-----	---	---				PANDUIT CORP. TINLEY PARK, ILLINOIS	
6	4-4-06	JCST	JKG	J. ADDED DIMENSION I. CHANGED VIEW: ADDED TAPE				38086-03	JKG	JKG					
5	4-13-05	JCST	JKG	H. CHANGED PART # (COLOR CHANGE-WAS GR-GRAY/GREEN) G. CHANGED MATERIAL				38086-03	HIW	HIW				FLEXIBLE DUCT SIZES: 12.5mm, 25mm, 50mm CUSTOMER DRAWING F	
4	7-26-04	JCST	JKG	F. CHANGED MATERIAL AND TITLE				38086-03	HIW	HIW					
3	3-29-04	JCST	JKG	E. REMOVED PARTS FROM CHART				38086-03	HIW	HIW				UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .04 (1.0) (.XXX) ± (.XX) ± .03 (1.8) ANGLES ±	
2	2-27-02	JCST	JKG	D. CHANGED VIEWS AND DIMENSIONS C. ADDED SHEET 2				38086-03	RTFI	RTFI				UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
I	8-10-01	JCST	JKG	B. CHANGED TAPE DIMENSION FOR 12X12 DUCT A. ADDED BOTTOM VIEWS AND NOTE 4 & 5				38086-03	RTFI	RTFI				DRAWN BY JCST DATE 4-10-01 CHK'D JKG	
R	4-10-01	JCST	JKG	RELEASED TO PRODUCTION				38086-03	HIW	HIW				MAT'L: POLYPROPYLENE G F	
REV	DATE	BY	CHK	DESCRIPTION				ECN	- R	CUST	SUP			SCALE NONE DRAWING NO. 38086-03 SHT. 1 OF 2 DWG A SIZE	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.





PANDUIT P/N	B x H	Bi x Hi	C	D	E	TAPE QTY. W x T	WEIGHT	PKG. QTY.
FL12X12LG-A	.5 X .5 (12.5 X 12.5)	.4 X .4 (10.3 X 10.6)	.04 (1.1)	.04 (1.0)	.04 (0.9)	1 .24 (6) x .04 (1)	0.03LB/ea 12.3g/ea	112
FL25X25LG-A	1.0 X 1.0 (25 X 25)	.9 X .9 (21.8 X 22.3)	.06 (1.6)	.06 (1.5)	.05 (1.2)	1 .58 (15) x .04 (1)	0.07LB/ea 33.3g/ea	70
FL50X50LG-A	2.0 X 2.0 (50 X 50)	1.8 X 1.8 (45.0 X 46.1)	.10 (2.5)	.09 (2.2)	.07 (1.7)	2 .58 (15) x .04 (1)	0.23LB/ea 103.3g/ea	32



CAD FILENAME/LAYERS		D38086BC_DC_FL50X50_00G.PRT	
PANDUIT		CORP. TINLEY PARK, ILLINOIS	
FLEXIBLE DUCT		SIZES: 12.5mm, 25mm, 50mm 	
CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .04 (1.0) (.XXX) ± (.XX) ± .03 (.8) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY JCST	MAT'L:		SCALE NONE
DATE 4-10-01	POLYPROPYLENE		DRAWING NO. 38086-03
CHK'D JKG	 		DWG A SHT. 2 OF 2 SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP
6	4-4-06	JCST	JKG	SEE SHEET # 1	38086-03	JKG	JKG	
5	4-13-05	JCST	JKG	SEE SHEET # 1	38086-03	HIW	HIW	
4	7-26-04	JCST	JKG	SEE SHEET # 1	38086-03	HIW	HIW	
3	3-29-04	JCST	JKG	SEE SHEET # 1	38086-03	HIW	HIW	
2	2-27-02	JCST	JKG	SEE SHEET # 1	38086-03	RTF	RTF	
1	8-10-01	JCST	--	SEE SHEET # 1	38086-03	--	--	
R	4-10-01	JCST	--	SEE SHEET # 1	38086-03	--	--	