

TXK

+105°C, High
Voltage Low
Impedance Long
Life, 5000 hours

Capacitance (μF)	WVDC	IC PART NUMBER	Maximum ESR (mΩ) 120 Hz, +20°C	Impedance Ω +20°C/- 10°C 100kHz	Maximum RMS Ripple Current (A) 100 kHz, +105°C	Dims DxL (mm)
3.3	450	335TXK450M	120.572		150	10x20
4.7	450	475TXK450M	84.657		190	12.5x20
10	250	106TXK250M	24.868		240	10x20
10	350	106TXK350M	39.789		220	10x20
10	400	106TXK400M	39.789		290	10x20
10	450	106TXK450M	39.789		300	12.5x25
22	160	226TXK160M	11.304		350	10x20
22	200	226TXK200M	11.304		350	10x20
22	250	226TXK250M	11.304		380	12.5x20
22	350	226TXK350M	18.086		340	12.5x20
22	400	226TXK400M	18.086		460	12.5x25
22	450	226TXK450M	18.086		450	16x25
33	160	336TXK160M	7.536		430	10x20
33	200	336TXK200M	7.536		460	12.5x20
33	250	336TXK250M	7.536		510	12.5x25
33	350	336TXK350M	12.057		460	12.5x25
33	400	336TXK400M	12.057		620	12.5x25
33	450	336TXK450M	12.057		620	16x31.5
47	160	476TXK160M	5.291		550	12.5x20
47	200	476TXK200M	5.291		550	12.5x20
47	250	476TXK250M	5.291		610	12.5x25

Capacitance (μF)	WVDC	IC PART NUMBER	Maximum ESR (mΩ) 120 Hz, +20°C	Impedance Ω +20°C/- 10°C 100kHz	Maximum RMS Ripple Current (A) 100 kHz, +105°C	Dims DxL (mm)
47	350	476TXK350M	8.466		560	16x25
47	400	476TXK400M	8.466		740	16x25
47	450	476TXK450M	3.657		780	18x31.5
68	160	686TXK160M	3.657		730	12.5x25
68	200	686TXK200M	3.657		730	12.5x25
68	250	686TXK250M	3.657		730	16x25
68	350	686TXK350M	5.851		740	16x31.5
68	400	686TXK400M	5.851		990	16x31.5
68	450	686TXK450M	5.851		990	18x35.5
100	160	107TXK160M	2.487		890	16x25
100	200	107TXK200M	2.487		890	16x25
100	250	107TXK250M	2.487		980	16x31.5
100	350	107TXK350M	3.979		1010	18x35.5
100	400	107TXK400M	3.979		1350	18x35.5
150	160	157TXK160M	1.658		1210	16x31.5
150	200	157TXK200M	1.658		1210	16x31.5
150	250	157TXK250M	1.658		1290	18x31.5
220	160	227TXK160M	1.13		1460	16x31.5
220	200	227TXK200M	1.13		1640	18x35.5
220	250	227TXK250M	1.13		1730	18x40
330	160	337TXK160M	0.754		2010	18x35.5

IC ILLINOIS CAPACITOR, INC.

3757 W. Touhy Ave., Lincolnwood, IL 60712 • (847)675-1760 • Fax (847) 675-2850 • www.illcap.com