

**Two-Piece - Inner sleeve****T&B Catalog Number:**

GSB670

UPC Number:

78621081331

Status:

Active

Description:

Two-Piece - Inner sleeve Copper Grounding Connector for shielded and coaxial cables, Inner Diameter .67, Length 5/16 inch, Gray

Features

Shielded cable grounding system made of 2 cylindrical sleeves (inner sleeve + outer sleeve), for solderless crimp connection. Inner sleeve for the Circular Range (the corresponding outer sleeve is crimped with a hydraulic head and the result is a circular-shaped crimp), for grounding multiple or overall shielded cables. The sleeves are color coded according to their size. Applications in communications, aerospace, and electronics.

General

Material	Copper alloy ASTM B135
Finish	Electro-Tin plated (per MIL-T-102727A)
Color	Gray
Associated Outer Sleeve	GSC840

Dimension Information

Length (inches)	.598
Length (mm)	15.2
Inner Diameter (inches)	.670
Inner Diameter (mm)	17.02
Outer Diameter (inches)	.750
Outer Diameter (mm)	19.05

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	250
T&B Sold in UOM	Each
T&B Weight Per UOM	2 lbs. per 100

Application Support

Overview	Available on Website
Installation Overview	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com