

# HC-B-G-M25-PLRBK

Order No.: 1407670



<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=1407670>

EVO plastic cable gland with bayonet locking; size M25

## Commercial data

|                        |                 |
|------------------------|-----------------|
| EAN                    | 4 046356 776387 |
| Pack                   | 1               |
| Customs tariff         | 39269097        |
| Gross weight in pieces | 40.72 g         |
| Country of Origin      | PL              |

## Product notes

WEEE/RoHS-compliant since:  
03/07/2012



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

## Technical data

### General data

|                               |           |
|-------------------------------|-----------|
| Type of the screw connection  | 1x M25    |
| Cable gland material          | Polyamide |
| Seal material                 | NBR       |
| Cable seal material           | NBR       |
| Wrench size, union nut        | 26 mm     |
| Thread type connection side 1 | Bayonet   |

|                                         |                   |
|-----------------------------------------|-------------------|
| External cable diameter                 | 9 mm ... 17 mm    |
| Tightening torque, union nut            | 6.00 Nm           |
| Inflammability class according to UL 94 | V0                |
| Degree of protection                    | IP65              |
| Ambient temperature (operation)         | -40 °C ... 100 °C |

### Certificates

Certification


Certifications applied for:

Certification Ex:

---

### Drawings

Dimensioned drawing



Dimensional drawing

**Address**

PHOENIX CONTACT Ltd  
Halesfield 13  
Telford / Shropshire / TF7 4PG, England  
Phone 01952 681 700  
Fax 01952 681 799  
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.  
Technical modifications reserved;