



RF400BA13

BeO Flanged Resistor

Power: 400 Watts (CW)



Resistance: $100\ \Omega \pm 5\%$

Frequency Range: DC to 1.0 GHz

Substrate: BeO



TYPICAL PERFORMANCE




For detailed information regarding this product or sample request contact Johanson Sales



Johanson Manufacturing Corporation • 301 Rockaway Valley Road, Boonton, New Jersey 07005 • Phone 973.334.2676 • Fax 973.334.2954
STAY TUNED • ELECTRONIC ACCURACY THROUGH MECHANICAL PRECISION • WWW.JOHANSONMFG.COM

OCT 08

BeO Flanged Resistor



CAUTION

**THIS SUBSTRATE USES BERYLLIUM OXIDE
USE CARE WHEN HANDLING.
DO NOT SCRATCH OR ABRASIVE
TRIM IN OPEN AREA.**

For detailed information regarding this product or sample request contact Johanson Sales

