

Conductor marking collar - PMH 3:GROSSBUCHSTABEN - 0800556

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor marking collar, yellow, labeled, Horizontal: Upper case letters, Mounting type: Thread on, Cable diameter: 5-9 mm, Lettering field: 4.2 x 2.6 mm

The illustration shows a combination of upper case letters, symbols and figures in versions PMH -0, -2 and -4

Key commercial data

Packing unit	1 pc
Minimum order quantity	50 pc
GTIN	 4 017918 006112
Weight per Piece (excluding packing)	0.59 GRM
Custom tariff number	39269097
Country of origin	Czech Republic

Technical data

Dimensions

Length (b)	6.6 mm
Height	9.5 mm
Width (a)	4.2 mm

Ambient conditions

Ambient temperature (operation)	-45 °C ... 70 °C
Ambient temperature (assembly)	> 10 °C

General

Note	Please specify the required marking with order: Minimum order per imprint: 1 packing unit
Color	yellow
Components	free from silicone, halogen and cadmium
Inflammability class according to UL 94	V0

Conductor marking collar - PMH 3:GROSSBUCHSTABEN - 0800556

Technical data

General

Material	EVA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Printing direction	Horizontal
Printing	Upper case letters
Marking mounting type	Thread on

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27400401
eCl@ss 5.1	27400401
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410