


3.5 mm×2.9 mm Side-operational SMD

Light Touch Switches

Type: **EVQP7/EVQP3/EVQ9P7**




■ Features

- External dimensions : 3.5 mm×2.9 mm, Height 1.35 mm
- A wide range of terminal type : L-shape, J-bent, Straight
- High mount ability
- Push plate strength enhanced type

■ Recommended Applications

- Car navigation, Car audio


■ Explanation of Part Numbers




■ Specifications



Type		Snap action / Push-on type SPST
Electrical	Rating	10 μ A 2 Vdc to 50 mA 12 Vdc (Resistive load)
	Contact Resistance	500 m Ω max.
	Insulation Resistance	100 M Ω min. (at 100 Vdc)
	Dielectric Withstanding Voltage	250 Vac (1 minute)
	Bouncing	10 ms max. (ON, OFF)
Mechanical	Operating Force	1.6 N, 2.2 N
	Push Travel	0.2 mm
	Push Strength	30 N (1 minute)
Endurance	Operating Life	100000 cycles min.
Operating Temperature		-20 °C to +70 °C
Storage Temperature		-40 °C to +85 °C (Bulk)
		-20 °C to +60 °C (Taping)
Minimum Quantity/Packing Unit		5000 pcs. Embossed Taping (Reel Pack)
Quantity/Carton		25000 pcs.



■ Dimensions in mm (not to scale)

No. 1 EVQP7A EVQP7J (Embossed Taping) With straight terminals Without boss 				
Part Numbers	Operating Force	Height	Push Plate Color	Operating Life
EVQP7A01K	2.2 N	1.35 mm	Black	100000 cycles
EVQP7J01K	1.6 N	1.35 mm	Black	100000 cycles







No. 2 EVQP7C EVQP7L (Embossed Taping) With straight terminals With boss 				
Part Numbers	Operating Force	Height	Push Plate Color	Operating Life
EVQP7C01K	2.2 N	1.35 mm	Black	100000 cycles
EVQP7L01K	1.6 N	1.35 mm	Black	100000 cycles

■ Dimensions in mm (not to scale)


No. 3 EVQP7B EVQP7K (Embossed Taping) With J-bent terminals Without boss 		 		
Part Numbers	Operating Force	Height	Push Plate Color	Operating Life
EVQP7B01K	2.2 N	1.35 mm	Black	100000 cycles
EVQP7K01K	1.6 N	1.35 mm	Black	100000 cycles

No. 4 EVQP7D EVQP7M (Embossed Taping) With J-bent terminals With boss 		 		
Part Numbers	Operating Force	Height	Push Plate Color	Operating Life
EVQP7D01K	2.2 N	1.35 mm	Black	100000 cycles
EVQP7M01K	1.6 N	1.35 mm	Black	100000 cycles


■ Dimensions in mm (not to scale)

No. 5 EVQP3 EVQ9P (Embossed Taping) With L-shape terminals Without boss 	     Circuit diagram  PWB land pattern for reference			
Part Numbers	Operating Force	Height	Push Plate Color	Operating Life
EVQP3401K	2.2 N	1.35 mm	Black	100000 cycles
EVQ9P701K	1.6 N	1.35 mm	Black	100000 cycles

■ Recommended Reflow Soldering Conditions



● Embossed Carrier Taping



● Straight terminals, L-shape terminals type

Unit: mm


Part No.	Height	A	B	W	F	E	P ₁	P ₂	P ₀	D ₀ Dia.	t ₁	t ₂
EVQP7, EVQP3 EVQ9P7	1.35	5.2±0.2	4.5±0.2	12.0±0.3	5.5±0.1	1.75±0.10	8.0±0.1	2.0±0.1	4.0±0.1	1.5 ^{+0.1} ₋₀	0.3±0.1	1.5±0.2

● J-bent type

Unit: mm

Part No.	Height	A	B	W	F	E	P ₁	P ₂	P ₀	D ₀ Dia.	t ₁	t ₂
EVQP7, EVQP3	1.35	4.5±0.2	4.5±0.2	12.0±0.3	5.5±0.1	1.75±0.10	8.0±0.1	2.0±0.1	4.0±0.1	1.5 ^{+0.1} ₋₀	0.3±0.1	1.5±0.2

● Standard Reel Dimensions in mm (not to scale)



Item	A	B	C	D	E
Rate (mm)	φ380.0±2.0	φ80.0±1.0	φ13.0±0.5	φ21.0±1.0	2.0±0.5
Item	W	T	t	r	
Rate (mm)	13.5±1.0	17.5±1.0	1.0 to 3.0	1.0±0.5	