


Locking DC Power Plugs

171-0721, 171-0725

KOBICONN

Locking DC Power Plugs



Dimensions: mm (In.)

SPECIFICATIONS	
Rating:	18VDC 1.5A
Insulation resistance:	100MΩ min. @ 500VDC
Dielectric strength:	500VAC for 1 minute
Sleeve:	nickel plated brass
Contact:	nickel plated brass
Terminal:	nickel plated brass
Metal:	nickel plated brass
Insulator:	POM (polyacetal type S761)
Handle:	Polyethylene

Date Last Revised: 6-27-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300476

171-0721, 171-0725

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[171-0721](#) [171-0725](#)