


Part Number: **5680123312F**

General Description	
Series	568
Configuration	3 mm Lens
Description	3 mm Quad-Level CBI Y-Y-R-G
Package Options	Bulk Packaging
Lamp Type	Quad Level Housing
Viewing	Right Angle
Polarity	Cathode Right
Lens Style	Tinted, Diffused
Viewing Angle	104
LED Centerline	2.54mm

Absolute Maximum Ratings (Ta = 25)	
Solder Temperature	260 for 5 secs
Operating Temperature	-55 to +100
Storage Temperature	-55 to +100

Operating Characteristics			
	LED Position: 1,2	LED Position: 3	LED Position: 4
Color	Yellow	Red	Green
LED Type	High Efficiency	High Efficiency	High Efficiency
Peak Wave Length	585	635	565
Luminous Intensity Min	3.2	1.1	2.2
Luminous Intensity Typical		3.7	
Forward Voltage Typical	2.1	2.1	2.1
Forward Voltage Max	2.8	2.8	2.8
Power Dissipation Max	60mW	100mW	100mW



5680123312F

check stock



[This is a
RoHS Compliant Product
To learn more click here](#)