




- VDC: 12, 24
- RPM: 5500~10000
- CFM: 6.63~12.74
- Impeller: 5 blades
- Rotational direction CCW view from front face
- PBT94V-0 frame and impeller
- AWG 26; UL 1007 lead wires
- Mass: 41.5g




DC FAN

40x40x28mm

Specification

	Bearing	Voltage	Current	Speed	Input Power	Air Flow	Static Pressure	Noise	Weight
MODEL NO	○ Sleeve ● One ball and one sleeve ○ Hydraulic	(Vdc)	(Amp)	(Rpm)	(Watts)	(CFM)	(mm/H ₂ O)	dB(A)	Gram
D4028B24H	●	24	0.130	10000	3.12	12.74	15.10	43.3	41.5
F4028B12L	●	12	0.065	5500	0.78	6.63	4.57	28.6	41.5
F4028B12H	●	12	0.250	10000	3.00	12.74	15.10	43.3	41.5

Design specifics subject to change without notice.



STATIC PRESSURE

