



PRODUCT No.	CUSTOMER P/N
10095509-P0003YYLF	3DB 16023 AAAA



CN1 CN2



Ink Jet Marking 5

NOTES:

- 100% CONTINUITY TEST FOR OPEN, SHORTING, ETC..
- HI-POT TEST: DC 300V/10ms
CONNECTION RESISTANCE: 0.5 Ohm MAX.
INSULATION RESISTANCE: 50M Ohm MIN.
- MATERIAL:

2	IDC CONNECTOR, 15X2, 2MM PITCH, FCI: 89947-730LF.	2	EA
1	FLAT CABLE, UL2651, 28AWGX30C, PITCH: 1MM, W/RED STRIP.	AR	MM
NO.	DESCRIPTION	Q'TY	UNIT

WIRING LIST

CN1	CN2
1	30
2	29
3	28
4	27
5	26
6	25
7	24
8	23
9	22
10	21
29	2
30	1

4. PART NUMBER SCHEME FOR CABLE ASSEMBLY:

10095509 - P 0 0 0 3 Y Y LF

LF: LEAD FREE

NOT APPLICABLE TO THIS ASS'Y

NOT APPLICABLE TO THIS ASS'Y

LENGTH (METERS & CENTIMETERS)
0003: 0 METERS 3 CENTIMETERSWIRE SIZE
P: 28AWG

5. BLACK INK JET ONTO THE MIDDLE OF CABLE,
THE CONTENT OF MARKING AS BELOW:

3DB 16023 AAAA	-- CUSTOMER P/N
FCI CHINA	-- MANUFACTURER
WWYY	-- DATE CODE (WEEK & YEAR)

6. ROHS COMPLIANCE

mat'l. code	surface ISO 1302	tolerance ISO 406 ISO 1101	projection ISO 1101	product family
ltr ecn no dr date	tolerances unless otherwise specified	angles linear	scale MM	title FLAT CABLE ASSEMBLY ALCATEL
A N10-0008 ST 1/12/10	±2°	±1.0	scale	dwg no 10095509 sheet 1 of 1 size A4
dr Sunny Tsai 9/23/08	engr Sunny Tsai 9/23/08	chr Jackson Wang 9/23/08	appo Jackson Wang 9/23/08	type CUSTOMER Drawing
sheet revision A	index sheet 1			