

# PANEL MOUNT INDICATOR, NON-RELAMPABLE

## NEON AND INCANDESCENT TECHNOLOGY

MOUNTING HOLE, Ø 0.500"

| PART NO.                       | LENS COLOR | VOLTAGE    | CURRENT [mA] | RATED LIFE HOURS |
|--------------------------------|------------|------------|--------------|------------------|
| <b>NEON 115VAC SERIES</b>      |            |            |              |                  |
| WL-1050A1                      | RED        | 105-125VAC | 1.5mA        | 25,000           |
| WL-1050A2                      | CLEAR      | 105-125VAC | 1.5mA        | 25,000           |
| WL-1050A3                      | AMBER      | 105-125VAC | 1.5mA        | 25,000           |
| WL-1050A4                      | WHITE      | 105-125VAC | 1.5mA        | 25,000           |
| WL-1052A5                      | GREEN      | 105-125VAC | 1.5mA        | 25,000           |
| WL-1052A6                      | BLUE       | 105-125VAC | 1.5mA        | 25,000           |
| <b>NEON 230VAC SERIES</b>      |            |            |              |                  |
| WL-1051A1                      | RED        | 208-250VAC | 1.5mA        | 25,000           |
| WL-1051A2                      | CLEAR      | 208-250VAC | 1.5mA        | 25,000           |
| WL-1051A3                      | AMBER      | 208-250VAC | 1.5mA        | 25,000           |
| WL-1051A4                      | WHITE      | 208-250VAC | 1.5mA        | 25,000           |
| WL-1053A5                      | GREEN      | 208-250VAC | 1.5mA        | 25,000           |
| WL-1053A6                      | BLUE       | 208-250VAC | 1.5mA        | 25,000           |
| <b>INCANDESCENT 12V SERIES</b> |            |            |              |                  |
| WL-1090A1-12V                  | RED        | 12V-14V    | 80mA         | 25,000           |
| WL-1090A3-12V                  | AMBER      | 12V-14V    | 80mA         | 25,000           |
| WL-1090A4-12V                  | WHITE      | 12V-14V    | 80mA         | 25,000           |
| WL-1090A5-12V                  | GREEN      | 12V-14V    | 80mA         | 25,000           |
| WL-1090A6-12V                  | BLUE       | 12V-14V    | 80mA         | 25,000           |
| <b>INCANDESCENT 28V SERIES</b> |            |            |              |                  |
| WL-1090A1-28V                  | RED        | 24V-28V    | 40mA         | 25,000           |
| WL-1090A3-28V                  | AMBER      | 24V-28V    | 40mA         | 25,000           |
| WL-1090A4-28V                  | WHITE      | 24V-28V    | 40mA         | 25,000           |
| WL-1090A5-28V                  | GREEN      | 24V-28V    | 40mA         | 25,000           |
| WL-1090A6-28V                  | BLUE       | 24V-28V    | 40mA         | 25,000           |

## NOTES

1. Recommended panel thickness  
0.030" to 0.090"
2. 6" leads with 1/2" strip are standard
3. Storage temperature  
TSTG: -25°C - +80°C
4. Ambient temperature  
TA: -20°C - +60°C
5. AC operation only for neon type
6. AC/DC operation for incandescent type
7. Voltage tolerance  
VOP: ± 10%
8. Body Material  
Nylon, white
9. Lens Material  
Polycarbonate
10. Bezel Material  
Stainless steel
11. Wire Gauge  
18 AWG
12. Wire Strip  
1/2"


## CERTIFICATIONS

UL (E340667), RoHS



**RoHS**  
COMPLIANT

## DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in inches

## OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

