

IPPC-6152A

**15" XGA TFT LCD Core™ 2 Quad /
Core™ 2 Duo Industrial Panel PC
with 2 x PCI Slots**



Introduction

The IPPC-6152A is an Industrial Panel PC with front USB access, supports the powerful Intel Core 2 Quad/Core 2 Duo, high speed DDR3 memory, two expansion PCI slots and slim type DVD-RW. The processor and chipset combination form the foundation of vPro, Intel's next generation digital office platform, offering remote out-of-band manageability, improved security, and energy efficient performance. Two SATA hard drive interfaces with RAID 0,1 support provides data security. The flat-sealed front panel design also allows easier cleaning and liquid run off. Also the control box has a gull-wing design for easy component installation and maintenance.

Specifications

General

▪ BIOS	AMI 4 MB Flash BIOS
▪ Certifications	UL, CE, FCC, CCC, BSMI
▪ Enclosure	Die-cast flat-sealed front with SGCC Housing
▪ Dimension (W x H x D)	449.92 x 315.63 x 142.7 mm (17.71" x 12.43" x 5.62")
▪ Mounting	Panel, Rack (option)
▪ OS Support	Windows 7, Windows XP
▪ Power Input	100 ~ 240 V _{AC} @ 60 ~ 50 Hz, 7 ~ 3.5 A
▪ Power Supply	350 W
▪ Weight (Gross)	13 Kg (18.6 lbs)

System Hardware

▪ CPU	Supports Socket LGA775 based up to Intel Core 2 Quad 2.8 GHz/Core 2 Duo 3.0 GHz
▪ Chipset	Intel Q45 GMCH/ICH10D0
▪ Memory	Two DDR3 240pin slots up to 4GB 1066/1333 MHz SDRAM
▪ LAN	10/100/1000 Base-T Ethernet x 2
▪ Expansion	2 x half-length PCI slots installed. (Replaceable with a 1 x two slot PCIEx1 riser accessory)
▪ Storage	Supports 2 x 2.5" SATA HDD Interface and Intel Matrix Storage Technology RAID 0/1
▪ Optical Driver	1 x Slim Type DVD-RW
▪ I/Os	2 x RS-232, 1 x RS-232/422/485 5 x USB 2.0 (one at front) 2 x PS2 (Keyboard, Mouse) 1 x VGA Port Mic-in, Line-in, Line-out

Features

- 15" XGA TFT LCD with touchscreen
- Intel® Core™ 2 Quad CPU (up to 2.8 GHz) / Core™ 2 Duo CPU (up to 3.0 GHz)
- System memory supports dual channel DDR3 SDRAM up to 4GB
- Offers two expansion slots (PCIe riser card optional) for PCI (PCIe) add-on cards
- Dual Gigabit Ethernet with Intel vPro technology
- Supports 2 x 2.5" SATA HDDs and RAID 0/1 compatibility
- Front USB access and system reset function
- Flat-sealed front panel
- Control box with gull-wing design for easy installation and maintenance
- Front panel is NEMA4/IP65 compliant
- Offers one slim type DVD-RW

LCD Display

▪ Backlight Life	50,000 hrs
▪ Contrast Ratio	700:1
▪ Display Size	15"
▪ Display Type	XGA TFT LCD
▪ Luminance	250 cd/m ²
▪ Max. Colors	16.2M (RGB 6-bit + FRC data)
▪ Max. Resolution	1024 x 768
▪ Viewing Angle (H/V°)	160/130

Touchscreen

▪ Lifespan	36 million with a silicone rubber of R8 finger, writing rate is by 250g at 2 times/s
▪ Light Transmission	> 80%
▪ Type	Analog resistive 5-wire

Environment


▪ Humidity	5 ~ 85% @ 40°C (non-condensing)
▪ Ingress Protection	Front panel: NEMA4/IP65
▪ Operating Temperature	0 ~ 50°C (32 ~ 122°F)
▪ Storage Temperature	-20 ~ 60°C (-4 ~ 140°F)
▪ Vibration Protection	5 ~ 500 Hz, 1 Grms random vibration

Ordering Information

- IPPC-6152A-R1AE 15" Core 2 Quad/Core 2 Duo Industrial Panel PC

Dimensions

Unit: mm




Panel Cut-out Dimensions: 424 x 293 mm

Accessories


- **IPPC-6152A-RMKE** IPPC-6152A/IPPC-6152F Rack Mount Kit
- **1702002600** Power Cable US Plug 1.8 M
- **1702002605** Power Cable EU Plug 1.8 M
- **1702031801** Power Cable UK Plug 1.8 M
- **1702031836** Power Cable China/Australia Plug 1.8 M

Note: A PCIe riser card is included in accessory box of IPPC-6152A-R1AE

Front Accessible USB Port



I/O View



CPU List

CPU Type List & Description		
Model Number	Advantech Part Number	Description
Intel Celeron E1400	96MPCL-2.0F8-5K7T	Celeron E1400 2.00GHz/512K/800
Intel Core2 Duo E4300	96MP2DD-18F8-2M7T	Core2 Duo E4300 1.80GHz EM64T Dual Core
Intel Core2 Duo E4400	96MP2DD-20F8-2M7T	Core2 Duo E4400 2.00GHz EM64T Dual Core
Intel Core2 Duo E4700	—	Core2 Duo E4700 2.60GHz EM64T Dual Core
Intel Core2 Duo E6550	—	Core2 Duo E6550 2.33GHz EM64T Dual Core
Intel Core2 Duo E6600	96MP2DD-24FA-4M7T	Core2 Duo E6600 2.40GHz EM64T Dual Core
Intel Core2 Duo E6750	96MP2DD-26FB-4M7T	Core2 Duo E6750 2.66GHz EM64T Dual Core
Intel Core2 Duo E7300	—	Core2 Duo E7300 2.66GHz EM64T Dual Core
Intel Core2 Duo E7400	96MP2DD-28FA-3M7T1	Core2 Duo E7400 2.80GHz EM64T Dual Core
Intel Core2 Duo E8400	96MP2DD-3FB-6M7T1	Core2 Duo E8400 3.00GHz EM64T Dual Core
Intel Core2 Quad Q6600	96MP2QD-24FA-8M7T	Core2 Quad Q6600 2.40GHz EM64T Quad Core
Intel Core2 Quad Q8200	96MP2QD-23FB-4M7T	Core2 Quad Q8200 2.33GHz EM64T Quad Core
Intel Core2 Quad Q9300	—	Core2 Quad Q9300 2.50GHz EM64T Quad Core
Intel Core2 Quad Q9400	96MP2QD-26FB-6M7T	Core2 Quad Q9400 2.66GHz EM64T Quad Core

Memory List

Memory Type List & Description		
Model Number	Advantech Part Number	Description
Apacer 78.01GC6.AF0	96D3-1G1333NN-AP1	1G DDR3-1333 240PIN 128 x 8 HYX(G)
Apacer 78.A1GC3.421	96D3-2G1066NN-AP	2G DDR3-1066 240PIN 128 x 8 ELP(G)
Apacer 78.A1GC6.AF1	96D3-2G1333NN-AP4	2G DDR3-1333 240PIN 128 x 8 HYX(G)
Transcend TS5KNU28300-1S	96D3-2G1066NN-TR	2G DDR3-1066 240PIN 128 x 8 SAM(G)
Transcend TS5KNU28300-3E	96D3-2G1333NN-TR	2G DDR3-1333 240PIN 128 x 8 ELP(G)
Transcend TS2KNU28100-3E	96D3-1G1333NN-TR	1G DDR3-1333 240PIN 128 x 8 ELP(G)
Transcend TS5KNU28300-3S	96D3-2G1333NN-TR2	2G DDR3-1333 240PIN 128 x 8 SAM(G)
Note: Please use 128 x 8		