



### APC Replacement Battery Cartridge #110

Part Number: APCRBC110



#### Batteries & Runtime

Battery Volt-Amp-Hour Capacity	84
Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Battery mounting	Enclosed battery cabinet
Expected Battery Life (years)	3 - 5
RBC™ Quantity	1

#### Physical

Net Weight	2.50 KG
Maximum Height	105.00 mm
Maximum Width	151.00 mm
Maximum Depth	65.00 mm
Shipping Weight	2.95 KG

Shipping Width	175.00 mm
Shipping Height	89.00 mm
Shipping Depth	213.00 mm
Color	Black
Units per Pallet	100.00

#### **Environmental**

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95%
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95%
Storage Elevation	0-15000 meters

#### **Conformance**

Standard Warranty	1 year repair or replace
-------------------	--------------------------

#### **Sustainable Offer Status**

RoHS	Compliant
REACH	REACH: Contains No SVHCs
PEP	Available in Documentation tab
EOLI	Available in Documentation tab

\*