

CWC6153

SUPERSEDES: X115493-V7

REV

DOCUMENT

CHANGED BY


CHECK

 A

0005059

KR 26 APR 04

AK



CHARACTERISTICS		ELECTRICAL DATA		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE: ☒ US (inch) CUSTOMARY ☐ SI (mm) METRIC NO PLACE X ±.040 ±1 ONE PLACE .X ±.030 ±0,4 TWO PLACE .XX ±.015 ±0,15 THREE PLACE .XXX ±.005 ± ANGLES ± 5° ± RAW MATERIAL-COMMERCIAL STANDARD		DRAWN	KR	26 APR 04	Honeywell						
OPERATING FORCE----- 8 OZ MAX		CONTACT ARRANGEMENT S P N C				CHECK	AK	26 APR 04							
RELEASE FORCE ----- 2 OZ MIN		L156 11A 1/3HP 125, 250 OR 277 VAC 1/2A 125 VDC, 1/4A 250 VDC 4A 125 VAC "L" RL ®		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		TITLE SWITCH, BASIC									
DIFFERENTIAL TRAVEL----- .006~.016											SIZE	DWG TYPE	DRAWING NAME		REV
OVERTRAVEL ----- .050 MIN											B	I	V7-7B37E9-000-1		A
FREE POSITION ----- .625 MAX				THIRD ANGLE PROJECTION		DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED									
RELEASE TRAVEL ----- .010 MIN		PTC	ASME Y14.5M-1994			SCALE	2 : 1	WEIGHT	SHEET 1 OF 1						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V7-7B37E9-000-1](#)