

Inductors, Commercial, Molded, Axial Leaded



ELECTRICAL SPECIFICATIONS

Inductance Tolerance: $\pm 1\%$, $\pm 3\%$, $\pm 5\%$, $\pm 10\%$, $\pm 20\%$, other tolerances available on request

Insulation Resistance: 1000 M Ω minimum per MIL-STD-202, method 302, test condition B

Dielectric Strength: Per MIL-STD-202, method 301: 1000 V_{AC} for IM-2, IM-4, IM-6, IM-8, IM-9 and IM-10 200 V_{AC} for IM-1

TEST EQUIPMENT (1)

- H/P 4342A Q-meter
- Measurements corporation megacycle meter, model 59
- Wheatstone bridge

Note

(1) Test procedure per MIL-PRF-15305

MATERIAL SPECIFICATIONS

Encapsulant: Epoxy

Standard Terminals: IM-1 and IM-2: 24 AWG; IM-4, IM-6 and IM-9: 22 AWG; IM-8: 21 AWG; IM-10: 20 AWG, tinned copper

ENVIRONMENTAL PERFORMANCE		
TEST	CONDITIONS	SPECIFICATIONS
Barometric Pressure	C	MIL-STD-202, meth. 105
Thermal Shock	A-1	MIL-STD-202, meth. 107
Flammability	-	MIL-STD-202, meth. 111
Overload	-	MIL-PRF-15305
Low Temperature Storage	-	MIL-PRF-15305
Resistance to Soldering Heat	A	MIL-STD-202, meth. 210
Resistance to Solvents	-	MIL-STD-202, meth. 215

FEATURES

- Wide inductance range in small package
- Flame retardant coating
- Precision performance, excellent reliability, study construction
- Epoxy molded construction provides superior moisture protection
- Compliant to RoHS directive 2002/95/EC



RoHS
COMPLIANT


MECHANICAL SPECIFICATIONS

Terminal Strength: Per MIL-STD-202, method 211, test condition A: For IM-1, 3 lb pull; for IM-2, IM-4, IM-6, IM-8, IM-9 and IM-10, 5 lb pull and twist

Weight: IM-1 = 0.25 g max., IM-2 = 0.30 g max., IM-4 = 0.65 g max., IM-6 = 0.95 g max., IM-8 = 1.5 g max., IM-9 = 2.0 g max., IM-10 = 2.5 g max.

INDUCTANCE RANGE AND MILITARY STANDARD		
MODEL	INDUCTANCE RANGE (μ H)	
	MIN.	MAX.
IM-1	0.10	100
IM-2	0.022	0.082
	0.10	1
	1.2	27
	33	1000
IM-4	0.15	4.7
	5.6	33
	36	240
	270	1800
IM-6	0.10	2.7
	3.3	27
	33	220
	270	1000
IM-8	1100	3600
IM-9	68	150
IM-10	3900	10 000

DIMENSIONS in inches [millimeters]



MODEL		A (DIA.)	B	C (TYP.)	D (DIA.)
IM-1	Max.	0.086 [2.18]	0.210 [5.33]	1.62 [41.15]	0.0215 [0.546]
	Min.	0.070 [1.78]	0.190 [4.83]	1.38 [35.05]	0.0185 [0.470]
IM-2	Max.	0.105 [2.67]	0.260 [6.60]	1.63 [41.40]	0.0215 [0.546]
	Min.	0.085 [2.16]	0.240 [6.10]	1.25 [31.75]	0.0185 [0.470]
IM-4	Max.	0.165 [4.19]	0.385 [9.78]	1.63 [41.40]	0.027 [0.686]
	Min.	0.145 [3.68]	0.365 [9.27]	1.25 [31.75]	0.023 [0.584]
IM-6	Max.	0.200 [5.08]	0.450 [11.43]	1.63 [41.40]	0.027 [0.686]
	Min.	0.180 [4.57]	0.430 [10.92]	1.25 [31.75]	0.023 [0.584]
IM-8	Max.	0.225 [5.72]	0.570 [14.48]	1.63 [41.40]	0.030 [0.762]
	Min.	0.205 [5.21]	0.550 [13.97]	1.25 [31.75]	0.026 [0.660]
IM-9	Max.	0.260 [6.60]	0.570 [14.48]	1.63 [41.40]	0.027 [0.686]
	Min.	0.240 [6.10]	0.550 [13.97]	1.25 [31.75]	0.023 [0.584]
IM-10	Max.	0.250 [6.35]	0.750 [19.05]	1.63 [41.40]	0.034 [0.864]
	Min.	0.230 [5.84]	0.730 [18.54]	1.25 [31.75]	0.030 [0.762]

STANDARD ELECTRICAL SPECIFICATIONS

MODEL	IND. (μ H)	TOL. (%)	Q MIN.	TEST FREQUENCY Q (MHz)	SRF MIN. (MHz) ⁽¹⁾	DCR MAX. (Ω)	RATED DC CURRENT (mA) ⁽²⁾	
IM-1	0.10	± 10	35	25.0	680.0	0.13	895	PHENOLIC CORE
IM-1	0.12	± 10	35	25.0	650.0	0.15	835	
IM-1	0.15	± 10	35	25.0	560.0	0.18	760	
IM-1	0.18	± 10	35	25.0	540.0	0.21	705	
IM-1	0.22	± 10	30	25.0	500.0	0.25	645	
IM-1	0.27	± 10	30	25.0	440.0	0.38	525	
IM-1	0.33	± 10	25	25.0	410.0	0.49	460	
IM-1	0.39	± 10	25	25.0	380.0	0.59	420	
IM-1	0.47	± 10	25	25.0	340.0	0.62	410	
IM-1	0.56	± 10	40	25.0	250.0	0.18	510	IRON CORE
IM-1	0.68	± 10	40	25.0	215.0	0.20	485	
IM-1	0.82	± 10	40	25.0	200.0	0.22	465	
IM-1	1.0	± 10	40	25.0	190.0	0.25	435	
IM-1	1.2	± 10	35	7.9	170.0	0.28	410	
IM-1	1.5	± 10	40	7.9	150.0	0.49	310	
IM-1	1.8	± 10	40	7.9	135.0	0.56	290	
IM-1	2.2	± 10	45	7.9	130.0	0.72	257	
IM-1	2.7	± 10	45	7.9	110.0	0.85	236	
IM-1	3.3	± 10	45	7.9	100.0	1.2	198	
IM-1	3.9	± 10	50	7.9	95.0	1.5	178	
IM-1	4.7	± 10	55	7.9	88.0	2.1	150	
IM-1	5.6	± 10	55	7.9	78.0	2.8	130	
IM-1	6.8	± 10	55	7.9	69.0	3.2	122	
IM-1	8.2	± 10	45	7.9	52.0	4.4	104	
IM-1	10.0	± 10	45	7.9	47.0	5.2	95	
IM-1	12.0	± 10	40	2.5	31.0	3.0	126	
IM-1	15.0	± 10	40	2.5	26.0	3.4	118	
IM-1	18.0	± 10	40	2.5	23.0	3.8	112	
IM-1	22.0	± 10	45	2.5	20.0	4.3	105	
IM-1	27.0	± 10	45	2.5	17.0	4.7	100	
IM-1	33.0	± 10	45	2.5	15.0	5.2	95	
IM-1	39.0	± 10	45	2.5	13.5	6.8	83.5	
IM-1	47.0	± 10	45	2.5	12.5	8.2	76	
IM-1	56.0	± 10	45	2.5	11.5	10.0	69	
IM-1	68.0	± 10	45	2.5	10.5	11.5	64	
IM-1	82.0	± 10	45	2.5	10.0	16.0	54.5	
IM-1	100.0	± 10	45	2.5	9.5	17.5	52	
IM-2	0.022	± 10	50	50.0	900.0	0.025	2400	PHENOLIC CORE
IM-2	0.027	± 20	40	25.0	875.0	0.03	2200	
IM-2	0.033	± 10	40	25.0	850.0	0.035	2000	
IM-2	0.039	± 10	40	25.0	825.0	0.04	1900	
IM-2	0.047	± 10	40	25.0	800.0	0.045	1800	
IM-2	0.056	± 10	40	25.0	775.0	0.05	1700	
IM-2	0.068	± 10	40	25.0	750.0	0.06	1500	
IM-2	0.082	± 10	40	25.0	725.0	0.07	1400	
IM-2	0.10	± 10	40	25.0	680.0	0.08	1350	
IM-2	0.12	± 10	40	25.0	640.0	0.09	1270	
IM-2	0.15	± 10	38	25.0	600.0	0.10	1200	
IM-2	0.18	± 10	35	25.0	550.0	0.12	1105	
IM-2	0.22	± 10	33	25.0	510.0	0.14	1025	
IM-2	0.27	± 10	33	25.0	430.0	0.16	960	
IM-2	0.33	± 10	30	25.0	410.0	0.22	815	
IM-2	0.39	± 10	30	25.0	365.0	0.30	700	
IM-2	0.47	± 10	30	25.0	330.0	0.35	650	
IM-2	0.56	± 10	30	25.0	300.0	0.50	545	
IM-2	0.68	± 10	28	25.0	275.0	0.60	495	
IM-2	0.82	± 10	28	25.0	250.0	0.85	415	
IM-2	1.0	± 10	25	25.0	230.0	1.0	385	

Notes⁽¹⁾ Measured with full length lead⁽²⁾ Rated DC current based on maximum temperature rise as shown in table



STANDARD ELECTRICAL SPECIFICATIONS								
MODEL	IND. (μH)	TOL. (%)	Q MIN.	TEST FREQUENCY Q (MHz)	SRF MIN. (MHz) ⁽¹⁾	DCR MAX. (Ω)	RATED DC CURRENT (mA) ⁽²⁾	
IM-2	1.2	± 10	25	7.9	150.0	0.18	590	IRON CORE
IM-2	1.5	± 10	28	7.9	140.0	0.22	535	
IM-2	1.8	± 10	30	7.9	125.0	0.30	455	
IM-2	2.2	± 10	30	7.9	115.0	0.40	395	
IM-2	2.7	± 10	37	7.9	100.0	0.55	355	
IM-2	3.3	± 10	45	7.9	90.0	0.85	270	
IM-2	3.9	± 10	45	7.9	80.0	1.0	250	
IM-2	4.7	± 10	45	7.9	75.0	1.2	230	
IM-2	5.6	± 10	50	7.9	65.0	1.8	185	
IM-2	6.8	± 10	50	7.9	60.0	2.0	175	
IM-2	8.2	± 10	55	7.9	55.0	2.7	155	
IM-2	10.0	± 10	55	7.9	50.0	3.7	130	
IM-2	12.0	± 10	45	2.5	40.0	2.7	155	
IM-2	15.0	± 10	40	2.5	35.0	2.8	150	
IM-2	18.0	± 10	50	2.5	30.0	3.1	145	
IM-2	22.0	± 10	50	2.5	25.0	3.3	140	
IM-2	27.0	± 10	50	2.5	20.0	3.5	135	
IM-2	33.0	± 10	45	2.5	24.0	3.4	130	FERRITE CORE
IM-2	39.0	± 10	45	2.5	22.0	3.6	125	
IM-2	47.0	± 10	45	2.5	20.0	4.5	110	
IM-2	56.0	± 10	45	2.5	18.0	5.7	100	
IM-2	68.0	± 10	50	2.5	15.0	6.7	92	
IM-2	82.0	± 10	50	2.5	14.0	7.3	88	
IM-2	100.0	± 10	50	2.5	13.0	8	84	
IM-2	120.0	± 10	30	0.79	12.0	13	66	
IM-2	150.0	± 10	30	0.79	11.0	15	61	
IM-2	180.0	± 10	30	0.79	10.0	17	57	
IM-2	220.0	± 10	30	0.79	9.0	21	52	
IM-2	270.0	± 10	30	0.79	8.0	25	47	
IM-2	330.0	± 10	30	0.79	7.0	28	45	
IM-2	390.0	± 10	30	0.79	6.5	35	40	
IM-2	470.0	± 10	30	0.79	6.0	42	36	
IM-2	560.0	± 10	30	0.79	5.0	46	35	
IM-2	680.0	± 10	30	0.79	4.0	60	30	
IM-2	820.0	± 10	30	0.79	3.8	65	29	
IM-2	1000.0	± 10	30	0.79	3.4	72	28	
IM-4	0.15	± 20	50	25	525.0	0.03	2450	PHENOLIC CORE
IM-4	0.22	± 20	50	25	450.0	0.055	1810	
IM-4	0.33	± 20	45	25	360.0	0.09	1400	
IM-4	0.47	± 20	45	25	310.0	0.12	1225	
IM-4	0.56	± 10	50	25	280.0	0.135	1150	
IM-4	0.68	± 10	50	25	250.0	0.15	1100	
IM-4	0.82	± 10	50	25	220.0	0.22	900	
IM-4	1.0	± 10	50	25	200.0	0.29	785	
IM-4	1.2	± 10	33	7.9	180.0	0.42	650	
IM-4	1.5	± 10	33	7.9	160.0	0.50	600	
IM-4	1.8	± 10	33	7.9	150.0	0.65	525	
IM-4	2.2	± 10	33	7.9	135.0	0.95	435	
IM-4	2.7	± 10	33	7.9	120.0	1.20	385	
IM-4	3.3	± 10	33	7.9	110.0	2.0	300	
IM-4	3.9	± 10	33	7.9	100.0	2.30	280	
IM-4	4.7	± 10	33	7.9	90.0	2.60	260	
IM-4	5.6	± 10	45	7.9	60.0	0.32	495	
IM-4	6.8	± 10	50	7.9	55.0	0.50	395	
IM-4	8.2	± 10	50	7.9	50.0	0.60	360	
IM-4	10.0	± 10	55	7.9	45.0	0.90	290	
IM-4	12.0	± 10	65	2.5	42.0	1.10	265	
IM-4	15.0	± 10	65	2.5	40.0	1.40	240	

Notes⁽¹⁾ Measured with full length lead⁽²⁾ Rated DC current based on maximum temperature rise as shown in table

STANDARD ELECTRICAL SPECIFICATIONS

MODEL	IND. (μ H)	TOL. (%)	Q MIN.	TEST FREQUENCY Q (MHz)	SRF MIN. (MHz) ⁽¹⁾	DCR MAX. (Ω)	RATED DC CURRENT (mA) ⁽²⁾	
IM-4	18.0	± 10	75	2.5	34.0	2.25	185	IRON CORE
IM-4	22.0	± 10	75	2.5	30.0	2.50	175	
IM-4	27.0	± 10	60	2.5	25.0	2.60	170	
IM-4	33.0	± 10	65	2.5	19.0	3.0	165	
IM-4	36.0	± 5	60	2.5	15.5	2.50	180	
IM-4	39.0	± 5	60	2.5	14.5	2.60	176	
IM-4	43.0	± 5	60	2.5	13.7	2.70	172	
IM-4	47.0	± 5	55	2.5	13.0	2.75	170	
IM-4	51.0	± 5	55	2.5	12.7	2.85	167	
IM-4	56.0	± 5	55	2.5	12.0	3.00	164	
IM-4	62.0	± 5	55	2.5	11.5	3.15	160	
IM-4	68.0	± 5	55	2.5	11.0	3.30	156	
IM-4	75.0	± 5	55	2.5	10.5	3.70	147	
IM-4	82.0	± 5	50	2.5	10.3	3.90	143	
IM-4	91.0	± 5	50	2.5	10.0	4.30	136	
IM-4	100.0	± 5	50	2.5	9.5	4.50	133	
IM-4	110.0	± 5	60	0.79	8.9	4.90	128	
IM-4	120.0	± 5	65	0.79	8.7	5.20	124	
IM-4	130.0	± 5	65	0.79	8.5	5.45	121	
IM-4	150.0	± 5	65	0.79	8.0	6.05	114	
IM-4	160.0	± 5	65	0.79	7.5	6.40	111	
IM-4	180.0	± 5	65	0.79	7.0	6.75	108	
IM-4	200.0	± 5	65	0.79	6.5	7.10	106	
IM-4	220.0	± 5	65	0.79	6.2	7.45	103	
IM-4	240.0	± 5	65	0.79	5.9	7.80	101	
IM-4	270.0	± 5	65	0.79	5.7	11.0	129	
IM-4	300.0	± 5	65	0.79	5.4	11.5	125	
IM-4	330.0	± 5	65	0.79	5.1	12.0	123	
IM-4	360.0	± 5	65	0.79	4.8	15.5	108	
IM-4	390.0	± 5	65	0.79	4.5	16.3	105	
IM-4	430.0	± 5	65	0.79	4.2	17.1	102	
IM-4	470.0	± 5	65	0.79	3.9	17.9	100	
IM-4	510.0	± 5	65	0.79	3.7	18.8	98	
IM-4	560.0	± 5	65	0.79	3.5	24.7	85	
IM-4	620.0	± 5	65	0.79	3.3	25.9	83	
IM-4	680.0	± 5	55	0.79	3.1	27.2	81	
IM-4	750.0	± 5	55	0.79	2.9	28.6	79	
IM-4	820.0	± 5	55	0.79	2.7	30.0	77	
IM-4	910.0	± 5	55	0.79	2.5	31.5	76	
IM-4	1000.0	± 5	55	0.79	2.3	33.1	74	
IM-4	1100.0	± 5	30	0.25	2.1	43.5	64	PHENOLIC CORE
IM-4	1200.0	± 5	30	0.25	2.0	45.7	63	
IM-4	1300.0	± 5	30	0.25	1.9	49.0	61	
IM-4	1500.0	± 5	30	0.25	1.8	52.5	59	
IM-4	1600.0	± 5	30	0.25	1.7	54.0	58	
IM-4	1800.0	± 5	30	0.25	1.6	56.7	56	
IM-6	0.10	± 20	55	25.0	510.0	0.020	3600	
IM-6	0.12	± 20	55	25.0	510.0	0.025	3300	
IM-6	0.15	± 20	55	25.0	510.0	0.030	3000	
IM-6	0.18	± 20	55	25.0	450.0	0.030	2900	
IM-6	0.22	± 20	50	25.0	415.0	0.035	2800	
IM-6	0.27	± 20	50	25.0	380.0	0.050	2400	
IM-6	0.33	± 20	50	25.0	350.0	0.065	2000	
IM-6	0.39	± 20	50	25.0	320.0	0.080	1800	
IM-6	0.47	± 20	50	25.0	300.0	0.085	1700	
IM-6	0.56	± 10	50	25.0	270.0	0.125	1450	

Notes⁽¹⁾ Measured with full length lead⁽²⁾ Rated DC current based on maximum temperature rise as shown in table



STANDARD ELECTRICAL SPECIFICATIONS								
MODEL	IND. (μ H)	TOL. (%)	Q MIN.	TEST FREQUENCY Q (MHz)	SRF MIN. (MHz) ⁽¹⁾	DCR MAX. (Ω)	RATED DC CURRENT (mA) ⁽²⁾	
IM-6	0.68	± 10	45	25.0	250.0	0.150	1300	PHENOLIC CORE
IM-6	0.82	± 10	40	25.0	210.0	0.205	1100	
IM-6	1.0	± 10	40	25.0	200.0	0.290	930	
IM-6	1.2	± 10	30	7.9	180.0	0.400	785	
IM-6	1.5	± 10	30	7.9	170.0	0.485	700	
IM-6	1.8	± 10	30	7.9	150.0	0.740	580	
IM-6	2.2	± 10	30	7.9	140.0	0.970	505	
IM-6	2.7	± 10	30	7.9	120.0	1.20	460	
IM-6	3.3	± 10	30	7.9	70.0	0.140	990	IRON CORE
IM-6	3.9	± 10	30	7.9	65.0	0.155	870	
IM-6	4.7	± 10	30	7.9	60.0	0.210	745	
IM-6	5.6	± 10	30	7.9	50.0	0.280	645	
IM-6	6.8	± 10	30	7.9	50.0	0.375	560	
IM-6	8.2	± 10	30	7.9	48.0	0.440	540	
IM-6	10.0	± 10	30	7.9	42.0	0.605	440	
IM-6	12.0	± 10	50	2.5	36.0	1.05	370	
IM-6	15.0	± 10	55	2.5	30.0	1.20	310	
IM-6	18.0	± 10	60	2.5	30.0	1.95	255	
IM-6	22.0	± 10	60	2.5	24.0	2.20	240	
IM-6	27.0	± 10	65	2.5	22.0	2.75	205	
IM-6	33.0	± 10	75	2.5	20.0	3.5	185	
IM-6	39.0	± 10	75	2.5	18.0	3.8	176	
IM-6	47.0	± 10	75	2.5	16.0	4.0	170	
IM-6	56.0	± 10	75	2.5	15.0	4.4	164	
IM-6	68.0	± 10	75	2.5	12.0	4.7	156	
IM-6	82.0	± 10	75	2.5	10.0	5.3	143	
IM-6	100.0	± 10	65	2.5	8.0	6.0	133	
IM-6	120.0	± 10	65	0.79	6.0	5.0	124	
IM-6	150.0	± 10	65	0.79	5.4	5.8	118	
IM-6	180.0	± 10	65	0.79	5.0	6.6	114	
IM-6	220.0	± 10	65	0.79	4.7	7.4	112	
IM-6	270.0	± 5	65	0.79	5.6	8.2	110	
IM-6	300.0	± 5	65	0.79	5.3	8.7	107	
IM-6	330.0	± 5	65	0.79	5.0	9.1	105	
IM-6	360.0	± 5	65	0.79	4.7	9.6	102	
IM-6	390.0	± 5	65	0.79	4.5	10.0	100	
IM-6	430.0	± 5	65	0.79	4.3	10.6	97	
IM-6	470.0	± 5	65	0.79	4.0	11.1	95	
IM-6	510.0	± 5	65	0.79	3.8	11.6	93	
IM-6	560.0	± 5	65	0.79	3.6	12.3	91	
IM-6	620.0	± 5	60	0.79	3.5	13.0	88	
IM-6	680.0	± 5	60	0.79	3.4	13.7	85	
IM-6	750.0	± 5	60	0.79	3.3	14.4	83	
IM-6	820.0	± 5	60	0.79	3.1	15.1	81	
IM-6	910.0	± 5	60	0.79	2.9	15.8	79	
IM-6	1000.0	± 5	60	0.79	2.8	16.5	78	
IM-8	1100.0	± 5	60	0.25	2.8	21.0	78	IRON CORE
IM-8	1200.0	± 5	60	0.25	2.7	22.0	76	
IM-8	1300.0	± 5	60	0.25	2.6	23.0	75	
IM-8	1500.0	± 5	65	0.25	2.4	25.0	72	
IM-8	1600.0	± 5	65	0.25	2.3	26.0	70	
IM-8	1800.0	± 5	65	0.25	2.2	28.0	68	
IM-8	2000.0	± 5	65	0.25	2.1	29.0	67	

Notes⁽¹⁾ Measured with full length lead⁽²⁾ Rated DC current based on maximum temperature rise as shown in table

STANDARD ELECTRICAL SPECIFICATIONS

MODEL	IND. (μ H)	TOL. (%)	Q MIN.	TEST FREQUENCY Q (MHz)	SRF MIN. (MHz) ⁽¹⁾	DCR MAX. (Ω)	RATED DC CURRENT (mA) ⁽²⁾	
IM-8	2200.0	± 5	70	0.25	2.0	30.0	66	IRON CORE
IM-8	2400.0	± 5	70	0.25	1.9	31.0	64	
IM-8	2700.0	± 5	70	0.25	1.8	33.0	62	
IM-8	3000.0	± 5	70	0.25	1.7	35.0	61	
IM-8	3300.0	± 5	70	0.25	1.6	38.0	58	
IM-8	3600.0	± 5	70	0.25	1.5	40.0	57	
IM-9	68.0	± 10	70	2.5	13.0	3.3	168	IRON CORE
IM-9	82.0	± 10	65	2.5	11.7	3.5	162	
IM-9	100.0	± 10	65	2.5	10.7	3.8	155	
IM-9	120.0	± 10	75	0.79	9.3	4.7	142	
IM-9	150.0	± 10	75	0.79	8.3	5.3	132	
IM-10	3900.0	± 5	80	0.25	1.45	44.0	61	IRON CORE
IM-10	4300.0	± 5	80	0.25	1.40	46.0	59	
IM-10	4700.0	± 5	80	0.25	1.35	48.0	58	
IM-10	5000.0	± 5	80	0.25	1.30	50.0	57	
IM-10	5600.0	± 5	80	0.25	1.25	53.0	56	
IM-10	6200.0	± 5	80	0.25	1.20	56.0	54	
IM-10	6800.0	± 5	80	0.25	1.15	59.0	52	
IM-10	7500.0	± 5	80	0.25	1.10	62.0	51	
IM-10	8200.0	± 5	80	0.25	1.05	65.0	50	
IM-10	9100.0	± 5	80	0.25	1.00	68.0	49	
IM-10	10 000.0	± 5	80	0.25	0.95	72.0	47	

Notes⁽¹⁾ Measured with full length lead⁽²⁾ Rated DC current based on maximum temperature rise as shown in table**ORDERING INFORMATION**

IM-2 MODEL	10 μ H INDUCTANCE VALUE	$\pm 10\%$ INDUCTANCE TOLERANCE	ER PACKAGE CODE	e2 JEDEC LEAD (Pb)-FREE STANDARD
---------------	-----------------------------------	---------------------------------------	-----------------------	--

GLOBAL PART NUMBER

I	M	0	2	E	R	1	0	0	K
MODEL				PACKAGE CODE		INDUCTANCE VALUE			INDUCTANCE TOLERANCE



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.