

PRODUCT NUMBER

71600-YXXXLF

LEAD FREE, SEE NOTE 6

COLOR OPTION, SEE NOTE 1

TOTAL NB OF POSITION 04 TO 64
SEE SHEET 2

OPTIONAL STRAIN RELIEF
SEE SHEET 2

TRIANGLE INDICATES
POSITION 1
NOTE 5

LEFT POLARIZING
NOTE 5

CENTRAL KEY
NOTE 5

RIGHT POLARIZING
NOTE 5

NOTES:

1 - HOUSING MATERIAL : GLASS FILLED
THERMOPLASTIC. UL94V-0 COLOR: GREY

= STANDARD COLOR GREY
B = OPTION COLOR BLACK

2 - PIN MATERIAL : PHOSPHOR BRONZE

3 - PRODUCT PACKAGED IN TUBES.

4 - TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS $N \times 2.54 = 20.32\text{mm}$

5 - 2x5, 2x6, 2x7 HAVE NO LEFT POLARIZING SLOT.

- 2x2, 2x3 WITH CENTRAL KEY HAVE NO TRIANGLE, NO
LEFT AND RIGHT POLARIZING SLOT.




- 2x2 WITHOUT CENTRAL KEY HAS NO LEFT AND RIGHT
POLARIZING SLOT.

- 2x3, 2x4 WITHOUT CENTRAL KEY HAVE NO LEFT POLARIZING SLOT

- 2x4 WITH CENTRAL KEY HAVE NO LEFT AND RIGHT POLARIZING SLOT

6 - THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS PER GS-22-008.

PACKAGING SPECIFICATION AS PER GS-14-920.




D-D SECTION


mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 406 ISO 1101	projection mm	product family 2.54MM IDC
lfr	ecn	no	dr	date	tolerances unless otherwise specified		title
AP	F12-0046	LMU	12.04.25		angles	X.X ±0.3	QUICKIE III FEM
AR	B-17851	LMU	14.06.05		linear	X.XX ±0.13	0.76μm Au
AS	F-26816	LMU	17.06.06			X.XXX ±0.05	scale 5:1
AL	F06-0270	LMU	06.09.12	engr	D.LE	01.01.24	dwg no
AM	F06-0274	LMU	06.09.25	chr	P.NZ	01.01.24	71600
AN	F09-0233	LMU	09.12.15	appd	JF.N	01.01.24	sheet 1 of 2
sheet	revision	AS	AG				size
index	sheet	1	2				A3
							type
							CUSTOMER Drawing

STRAIN RELIEF OPTION AVAILABILITY	Nbr OF POSITIONS
1/6	04
0/1/2/3/6	06
0/1/2/3/6	08
0/1/2/3/6	10
0/1/2/3/6	14
0/1/2/3/6	16
0/1/2/3/6	18
0/1/2/3/6	20
0/1/3	24
0/1/2/3/6	26
0/1/2/3/6	30
0/1/2/3/6	34
0/1/2/3/6	40
0/1/2/3/6	50
0/1/2/3/6	60
0/1/2/3/6	64
PLATING 0.76µm GOLD ON CONTACT AREA 1.27 µm Ni REMAINDER OF PRODUCT	


624
304
204 / 224
004
DASHES NOT AVAILABLE




WITHOUT STRAIN RELIEF




WITH LOW PROFILE STRAIN RELIEF




WITH STANDARD STRAIN RELIEF




WITH LATCHING STRAIN RELIEF



LOW PROFILE
STRAIN RELIEF



STANDARD
STRAIN RELIEF



LATCHING STRAIN RELIEF
FOR SLIM HEADER

71600-6YY(B)LF	●					●
71600-3YY(B)LF		●	●			
71600-2YY(B)LF	●				●	
71600-1YY(B)LF	●			●		
71600-0YY(B)LF	●		●			
PRODUCT NUMBER	WITH CENTRAL KEY	WITHOUT	STANDARD	WITHOUT	LOW PROFILE	LATCHING
			STRAIN RELIEF			

mat'l. code				surface			tolerance		projection		product family	
				ISO 1302			ISO 406		ISO 1101		QUICKIE	
ltr ecn no dr date				tolerances unless otherwise specified							title	
AF B-17851 LMU 14.06.05				angles							IDC RECEPT	
AG F-26816 LMU 17.06.06				linear							DR	
AB F03019 DLE 03.01.23				dr			D.LE		01.01.24		dwg no	
AC F05-0180 LMU 05.04.22				engr			P.NZ		01.01.24		sheet 2 of - size	
AD F06-0270 LMU 06.09.12				chr			JF.N		01.01.24		71600	
AE F06-0274 LMU 06.09.25				appd			P.NZ		01.01.24		A3	
sheet index				revision sheet							type	
											CUSTOMER Drawing	

